

Housing - HC-B 16-SMQ-84/O1PG29 - 1460167

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




HEAVYCON B16 box mounting base, with double locking latch, height: 84 mm, with 1 x Pg29 gland

The figure shows the article as type B24

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 696654
GTIN	4046356696654
Weight per Piece (excluding packing)	440.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	84 mm
Width	57 mm
Length	117 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K
Size	B16

Housing - HC-B 16-SMQ-84/O1PG29 - 1460167


Technical data

General

Housing type	Box mounting bases
Locking type	With double locking latch
No. of cable outlets	1
Cable exit	lateral
Screw connection	none
Type of the screw connection	1x Pg29
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA
Assembly instructions	For half and full screw connections

Drawings

Dimensional drawing



Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Housing - HC-B 16-SMQ-84/O1PG29 - 1460167

Approvals

EAC



7500651.22.01.00246