

Contact insert module - HC-M-08-GBIT-MOD-ST - 1587690


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug module for Gigabit connector (8-pos.; for CAT5)



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 528276
GTIN	4046356528276
Weight per Piece (excluding packing)	10.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	40.85 mm
Width	34.2 mm
Length	14.6 mm

Electrical characteristics

Connection profile	8
--------------------	---

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (including heating up of contacts)
---------------------------------	---

Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Contact insert module - HC-M-08-GBIT-MOD-ST - 1587690

Technical data

General

Series	HC-M-08-GBIT
Number of module slots	1
Flammability rating according to UL 94	V0
Assembly instructions	Module for Order No. 1587713

Material data

Contact carrier material	PC
--------------------------	----

Standards and Regulations


Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Male insert

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

Contact insert module - HC-M-08-GBIT-MOD-ST - 1587690

Classifications

eCl@ss

eCl@ss 8.0	27440205
eCl@ss 9.0	27440205

ETIM

ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000438
ETIM 6.0	EC000438

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
mm ² /AWG/kcmil	22-20		
Nominal current I _N	5 A		
Nominal voltage U _N	30 V		

Contact insert module - HC-M-08-GBIT-MOD-ST - 1587690

Approvals

EAC		7500651.22.01.00246
-----	---	---------------------