

Sleeve housing - VC-K-T2-Z-FK-7,5X29,5 - 1607680

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, plastic, type: VC2, with 7.5 x 29.5 mm flat cable outlet, locking screws with positive/negative head,

The figure shows version VC-K-T3-Z

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 944070
GTIN	4017918944070
Weight per Piece (excluding packing)	61.760 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	65 mm
--------	-------

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 80 °C

General

Type	VC2
Degree of protection	IP54
Flammability rating according to UL 94	V0
Locking type	Screw locking, cylinder head
Fixing screws	M4

Sleeve housing - VC-K-T2-Z-FK-7,5X29,5 - 1607680

Technical data

General

Tightening torque, mounting screw	1.5 Nm \pm 0.3 Nm
Type of the screw connection	7.5 x 29.5 mm
Cable outlet	straight
Housing material	PA
Seal material	EPDM
Ambient temperature (operation)	-40 °C ... 80 °C

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000437
ETIM 5.0	EC000437
ETIM 6.0	EC000437
ETIM 7.0	EC000437

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501

Sleeve housing - VC-K-T2-Z-FK-7,5X29,5 - 1607680

Classifications

UNSPSC

UNSPSC 13.2	31261501
-------------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	--	---------

Accessories

Accessories

Protective cover

Protective covers - VC-SD2 - 1853683



VARIICON dust cover for panel mounting frame, with IP40 protection, type 2

Protective covers - VC-SD-T2 - 1886731



VARIICON protective cover for sleeve housing, with IP50 protection, type 2, max. tightening torque: 1.6 Nm
