

## Coupling - VS-PPC-F2-MSTB-POBK-1R-SPSA5 - 1608294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



MSTB panel mounting frame, IP67, for push-pull interlocking, plastic, with integrated contact insert for conductor connection, spring-cage connection, 24 V, for square mounting cutout, with grommet, without mounting screws



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	20.9 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### General data

Note	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
Rated current at 40°C	16 A
Rated voltage	24 V
Number of positions	5
Signal type/category	Universal
Degree of pollution	2

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Classifications

eCl@ss

eCl@ss 4.0	27250313
------------	----------

# Coupling - VS-PPC-F2-MSTB-POBK-1R-SPSA5 - 1608294

## Classifications

### eCl@ss

eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440210
eCl@ss 9.0	27440210

### ETIM

ETIM 3.0	EC001134
ETIM 4.0	EC002636
ETIM 5.0	EC002310

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

#### Approvals

EAC / UL Recognized / EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

### Approval details

EAC
-----

# Coupling - VS-PPC-F2-MSTB-POBK-1R-SPSA5 - 1608294


## Approvals

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	14
Nominal current I <sub>N</sub>	16 A
Nominal voltage U <sub>N</sub>	24 V

EAC
-----


## Drawings

Dimensional drawing



Push-Pull MSTB panel mounting frame

Dimensional drawing



Panel cutout