

## Cable gland - HC-M-KV-M25(14-21) - 1646007

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Metal screw connection up to 5 bar, thread length: 7 mm, cable diameter: 14 - 21 mm, WAF 34, screw connection: M25

Illustration shows the HC-M-KV-M32 version



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 941277
Weight per Piece (excluding packing)	75.816 g
Custom tariff number	74199990
Country of origin	Germany

### Technical data

#### Dimensions

Length	31 mm
Length without connecting thread	23.5 mm
Connecting thread diameter	25 mm
Wrench size, union nut	34 mm
Wrench size, support	34 mm
Hexagon angular dimension GRP	36 mm
Length of the connecting thread	7.5 mm
External cable diameter	14 mm ... 21 mm

#### Ambient conditions

Degree of protection	IP65
	IP65

# Cable gland - HC-M-KV-M25(14-21) - 1646007

## Technical data

### Ambient conditions

Ambient temperature (operation)	-30 °C ... 100 °C
---------------------------------	-------------------

### General

No. of conductors	1
Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
O-ring material	NBR
Shielded	No
Thread type on connection side	M25
Tightening torque, union nut	10.00 Nm
Color	silver

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

# Cable gland - HC-M-KV-M25(14-21) - 1646007

## Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

Approval details

EAC
-----

## Drawings

Dimensional drawing

