

D-SUB crimp contact - VS-BU-CD-HD-1,0/13,5/0,37 - 1655263

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, for D-SUB contact inserts with high density, socket, connection cross section AWG 22, turned, gold-plated



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	0.12 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	≥ 200
Connection method	Crimp connection
Type of contact	Crimp contacts
Conductor cross section	0.34 mm ²
Connection cross section AWG	22

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

Material data

Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel

Electrical characteristics

Rated current	3 A
---------------	-----

D-SUB crimp contact - VS-BU-CD-HD-1,0/13,5/0,37 - 1655263

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261202
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details

EAC


D-SUB crimp contact - VS-BU-CD-HD-1,0/13,5/0,37 - 1655263

Approvals

EAC

Drawings

Dimensional drawing



D-SUB crimp contact socket