

## D-SUB coaxial contact - VS-ST-KX-75-LP - 1655645

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coaxial contact, for D-SUB combination inserts, for PCB assembly, pin, angled, gold-plated

RoHS

### Key Commercial Data

Packing unit	10 pc
GTIN	
GTIN	4046356029537

### Technical data

#### Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
Connection method	PCB mounting
Type of contact	Coaxial
Insertion force per signal contact	≤ 7.00 N
Extraction force per signal contact	≤ 7 N
Insulation resistance	10 TΩ
Contact type	turned

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

#### Material data

Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel

#### Electrical characteristics

Rated current	2 A
Rated voltage (III/3)	250 V

#### Environmental Product Compliance

## D-SUB coaxial contact - VS-ST-KX-75-LP - 1655645

### Technical data

#### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Approvals

#### Approvals

---

Approvals


EAC

---

Ex Approvals

---

#### Approval details

EAC		B.01742
-----	---	---------

---

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>