

## Flush-type connector - SACC-CI-M12MSB-5CON-L180 THR - 1552230

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/actuator flush-type plug, 5-pos., B-coded, with straight THR solder connection, only contact insert



### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 60 pc    |
| Weight per Piece (excluding packing) | 3.45 g   |
| Custom tariff number                 | 85366990 |
| Country of origin                    | Germany  |

### Technical data

#### Ambient conditions

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket)                |
|                                 | -40 °C ... 85 °C (without mechanical actuation) |
| Degree of protection            | IP67                                            |

#### General

|                       |                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note                  | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Rated current at 40°C | 4 A                                                                                                                                                                                                                                                                                                                                                |
| Rated voltage         | 60 V                                                                                                                                                                                                                                                                                                                                               |
| Rated surge voltage   | 1.5 kV                                                                                                                                                                                                                                                                                                                                             |
| Number of positions   | 5                                                                                                                                                                                                                                                                                                                                                  |
| Insulation resistance | ≥ 100 MΩ                                                                                                                                                                                                                                                                                                                                           |
| Coding                | B - inverse                                                                                                                                                                                                                                                                                                                                        |
| Standards/regulations | M12 connector IEC 61076-2-101                                                                                                                                                                                                                                                                                                                      |

# Flush-type connector - SACC-CI-M12MSB-5CON-L180 THR - 1552230

## Technical data

### General

|                             |                                   |
|-----------------------------|-----------------------------------|
| Status display              | No                                |
| Overvoltage category        | II                                |
| Pollution degree            | 3                                 |
| Connection method           | THR solder connection             |
| Insertion/withdrawal cycles | > 100                             |
| Torque                      | 3 Nm ... 4 Nm (Installation-side) |
| Mounting type               | PCB mounting                      |
| Type of packaging           | Tray                              |

### Material

|                                        |            |
|----------------------------------------|------------|
| Flammability rating according to UL 94 | V0         |
| Contact material                       | CuZn       |
| Contact surface material               | Au         |
| Contact carrier material               | PA 66      |
| Sealing material                       | FKM / EPDM |

### Cable

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C (cable, fixed installation)    |
|                                 | -25 °C ... 85 °C (cable, flexible installation) |

### Standards and Regulations

|                                        |                 |
|----------------------------------------|-----------------|
| Standard designation                   | M12 connector   |
| Standards/regulations                  | IEC 61076-2-101 |
| Flammability rating according to UL 94 | V0              |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27143423 |
| eCl@ss 5.1 | 27143423 |
| eCl@ss 6.0 | 27143423 |
| eCl@ss 7.0 | 27449001 |
| eCl@ss 8.0 | 27440103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC002061 |
| ETIM 4.0 | EC002061 |

## Flush-type connector - SACC-CI-M12MSB-5CON-L180 THR - 1552230

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC002061 |
|----------|----------|

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |

### Approvals

#### Approvals

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

#### Approval details

|                                                                                                   |       |
|---------------------------------------------------------------------------------------------------|-------|
| UL Recognized  |       |
| mm²/AWG/kcmil                                                                                     | 26-20 |
| Nominal current I <sub>N</sub>                                                                    | 4 A   |
| Nominal voltage U <sub>N</sub>                                                                    | 60 V  |

|                                                                                                    |       |
|----------------------------------------------------------------------------------------------------|-------|
| cUL Recognized  |       |
| mm²/AWG/kcmil                                                                                      | 26-20 |
| Nominal current I <sub>N</sub>                                                                     | 4 A   |

# Flush-type connector - SACC-CI-M12MSB-5CON-L180 THR - 1552230

## Approvals


|                    |      |
|--------------------|------|
| Nominal voltage UN | 60 V |
|--------------------|------|

|     |
|-----|
| EAC |
|-----|

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| cULus Recognized  |
|----------------------------------------------------------------------------------------------------|


## Drawings

Schematic diagram




Pin assignment M12 male connector, 5-pos., B-coded, male side

Drilling diagram



Drilling diagram


Dimensional drawing



M12 male connector contact carrier

## Flush-type connector - SACC-CI-M12MSB-5CON-L180 THR - 1552230

Dimensional drawing



THR tray packaging