

Crimp contact - CK2,5-ED-1,50ST-S AG - 1663860


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Turned 2.5 crimp contact, individual pin contact, switching contact, 2 mm retarded, conductor cross section 1.50 mm², silver-plated



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 017918 123536 |
| Weight per Piece (excluding packing) | 1.22 g |
| Custom tariff number | 85389099 |
| Country of origin | Germany |

Technical data

Electrical characteristics

| | |
|------|--|
| Note | For HC-HV contact carriers, the quality of a crimp connection is determined by DIN EN 60 352-2 |
|------|--|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

Mechanical characteristics

| | |
|---|---------------------|
| Conductor cross section | 1.5 mm ² |
| Connection cross section AWG | 16 |
| Stripping length of the individual wire | 7.5 mm |
| Insertion/withdrawal cycles | ≥ 500 |

General

| | |
|------|-------------------------|
| Type | Individual male contact |
|------|-------------------------|

Crimp contact - CK2,5-ED-1,50ST-S AG - 1663860

Technical data

General

| | |
|-------------------|---|
| Series | HC-HV |
| Connection method | Crimp connection |
| Connection | for HC-M-06, HC-M-HV, HC-M-08, HC-M-20, HC-A, HC-BB, HC-B and HC-HV contact carriers. The quality of a crimp connection is determined by the DIN EN 60 352-2. |

Material data

| | |
|--------------------------|---------------|
| Contact material | Copper alloy |
| Contact surface material | silver-plated |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440204 |
| eCl@ss 8.0 | 27440204 |
| eCl@ss 9.0 | 27440204 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000796 |
| ETIM 3.0 | EC000796 |
| ETIM 4.0 | EC000796 |
| ETIM 5.0 | EC000796 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211923 |
| UNSPSC 7.0901 | 39121522 |
| UNSPSC 11 | 39121522 |
| UNSPSC 12.01 | 39121522 |
| UNSPSC 13.2 | 39121522 |

Approvals

Approvals

Crimp contact - CK2,5-ED-1,50ST-S AG - 1663860

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

| |
|-----|
| EAC |
|-----|

Drawings

Dimensional drawing

