

## Protective covers - HC-B 10-SD-ML/FS - 1678295


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective cover B10, with single locking latch, protective cover material: PA, height: 21.6 mm, seal: yes, With lanyard, diameter of retaining cord eyelet: 30 mm



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 151836
GTIN	4017918151836
Weight per Piece (excluding packing)	57.070 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Length	73 mm
Width	43 mm
Height	21.6 mm
Diameter of retaining cord eyelet	30 mm

#### Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	B10
Type	For sleeve housing without single locking latch

## Protective covers - HC-B 10-SD-ML/FS - 1678295

### Technical data

#### General

Material	PA
Seal material	NBR
Locking latch material	High-grade steel, handle: PA-GF
Flammability rating according to UL 94	HB
Color	gray
Seal present	yes
Connection	Plastic protective cover for short-term protection

#### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 5.1	27143400
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

#### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

#### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421

## Protective covers - HC-B 10-SD-ML/FS - 1678295

### Approvals

Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

---