

## Protective covers - HC-B 10-SD-MQT/FS-AL - 1584541

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Protective cover B10, with double locking latch, protective cover material: Al, height: 16.9 mm, seal: yes, With lanyard, diameter of retaining cord eyelet: 30 mm



COMPLETE

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 144131
GTIN	4046356144131
Weight per Piece (excluding packing)	104.850 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Length	73 mm
Width	43 mm
Height	16.9 mm
Diameter of retaining cord eyelet	30 mm

#### Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Size	B10
Type	for sleeve housing without double locking latch

## Protective covers - HC-B 10-SD-MQT/FS-AL - 1584541

### Technical data

#### General


Material	Aluminum, die-cast
Seal material	NBR
Locking latch material	High-grade steel, handle: PA-GF
Color	gray
Seal present	yes
Assembly instructions	Not for HC-B...EMC housings
Connection	The guide pins of the protective cover must be removed when using coding sockets, pins, and bolts.

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings

Dimensional drawing



Dimensional drawing

### Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208

# Protective covers - HC-B 10-SD-MQT/FS-AL - 1584541

## Classifications

### eCl@ss

eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

### ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002314
ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

---