

Cable gland - HC-M-KV-M16(5-9) - 1690558

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Metal screw connection up to 5 bar, thread length: 5 mm, cable diameter 5 - 9 mm, WAF 17, screw connection: M16

The illustration shows version HC-M-KV-M20



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 017918 822613
Weight per Piece (excluding packing)	19.18 g
Custom tariff number	74199990
Country of origin	Germany

Technical data

Dimensions

Wrench size, union nut	17 mm
Wrench size, support	17 mm
Length of the connecting thread	5 mm
External cable diameter	5 mm ... 9 mm

Ambient conditions

Degree of protection	IP68, to 5 bar
	IP68 (Up to 5 bar)
Ambient temperature (operation)	-20 °C ... 100 °C

General

Type of the screw connection	M16
------------------------------	-----

Cable gland - HC-M-KV-M16(5-9) - 1690558

Technical data

General

No. of conductors	1
Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
O-ring material	NBR
Shielded	No
Thread type on connection side	M16
Torque	5 Nm (Union nut)
Tightening torque, union nut	5.00 Nm

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441


UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Drawings

Cable gland - HC-M-KV-M16(5-9) - 1690558

Dimensional drawing



Dimensional drawing

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>