

## Housing - HC-B 16-SMQ-84/O1M32 - 1604793

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON box mounting base B16, with double locking latch, height 84 mm, with support 1xM32



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 882716
Weight per Piece (excluding packing)	468.5 GRM
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	84 mm
Width	57 mm
Length	117 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Type	B16
Housing type	Box mounting bases
Locking type	With double locking latch
No. of cable exits	1

# Housing - HC-B 16-SMQ-84/O1M32 - 1604793

## Technical data

### General

Cable exit	Lateral
Screw connection	none
Type of the screw connection	1x M32
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA
Assembly instructions	For half and full screw connections

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

# Housing - HC-B 16-SMQ-84/O1M32 - 1604793

## Approvals

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

## Approval details



## Drawings

Dimensioned drawing

