


Feed-through header - PC 5/ 6-GU-7,62 BK 4CP - 1700423

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB headers, number of positions: 6, pitch: 7.62 mm, color: black



The figure shows a 5-pos. version of the product



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 549448
GTIN	4046356549448
Weight per Piece (excluding packing)	12.400 g
Custom tariff number	85366930
Country of origin	Germany

Technical data

Dimensions

Length [l]	29.25 mm
Width	48.52 mm
Pitch	7.62 mm
Dimension a	38.1 mm
Width [w]	48.52 mm
Height [h]	17.74 mm
Height	13.54 mm
Length of the solder pin	4.2 mm
Pin spacing	7.62 mm
Length	29.25 mm

Feed-through header - PC 5/ 6-GU-7,62 BK 4CP - 1700423

Technical data

General

Range of articles	PC 5/..-GU
Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	630 V
Rated voltage (III/2)	630 V
Rated voltage (II/2)	800 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	41 A
Maximum load current	41 A
Insulating material	PA
Flammability rating according to UL 94	V0
Color	black
Number of positions	6

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

Feed-through header - PC 5/ 6-GU-7,62 BK 4CP - 1700423

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637
ETIM 6.0	EC002637
ETIM 7.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals


Approvals

EAC / cULus Recognized

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-19920722
	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	41 A	41 A	10 A

