

Base strip - PC 6-16/ 4-G-10,16 BK - 1708378

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 41 A, Number of positions: 4, Pitch: 10.16 mm, Color: black, Contact surface: Silver, Mounting: Wave soldering



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	16.48 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Pitch	10.16 mm
Dimension a	30.48 mm
Constructional height	14 mm
Length of the solder pin	5 mm

General

Range of articles	PC 6-16/..-G
Connection in acc. with standard	EN-VDE
Nominal current I_N	41 A
Color	black
Number of positions	4

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL

Classifications

eCl@ss

eCl@ss 4.0	272607xx
------------	----------

Base strip - PC 6-16/ 4-G-10,16 BK - 1708378

Classifications

eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / SEV / cUL Recognized / EAC / IECCEB Scheme / cULus Recognized

Ex Approvals

Approvals submitted


Approval details

UL Recognized 


Base strip - PC 6-16/ 4-G-10,16 BK - 1708378

Approvals

SEV

cUL Recognized 

EAC

IECEE CB Scheme 

Nominal current I _N	76 A
Nominal voltage U _N	1000 V

cULus Recognized 