

Base strip - IPCV 5/ 8-G-7,62 - 1708886

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 41 A, Rated voltage (III/2): 630 V, Number of positions: 8, Pitch: 7.62 mm, Color: green, Contact surface: Tin, Mounting: Wave soldering

The figure shows a 5-pos. version of the product

Product Features

- Asymmetrical arrangement of solder pins to prevent mismatching
- Inverted vertical IPC 5 headers for implementing a touch-proof PCB output or a PCB/PCB connection (in combination with PC 5 base strips)
- Maximum contact reliability due to integrated double steel spring



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	21.11 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Length	12.8 mm
Pitch	7.62 mm
Dimension a	53.34 mm
Constructional height	30.1 mm
Length of the solder pin	5 mm
Pin dimensions	1,2x0,8
Pin spacing	7.62 mm
Hole diameter	1.3 mm

Base strip - IPCV 5/ 8-G-7,62 - 1708886

Technical data

General

Range of articles	IPCV 5/...-G
Insulating material group	I
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	630 V
Rated voltage (III/2)	630 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	41 A
Maximum load current	41 A
Insulating material	PA
Flammability rating according to UL 94	V0
Color	green
Number of positions	8

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

Base strip - IPCV 5/ 8-G-7,62 - 1708886

Classifications

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals


Approvals


UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 			
	B	C	D
Nominal current I _N	41 A	41 A	5 A
Nominal voltage U _N	300 V	300 V	600 V

cUL Recognized 			
	B	C	D
Nominal current I _N	41 A	41 A	5 A
Nominal voltage U _N	300 V	300 V	600 V

EAC

Base strip - IPCV 5/ 8-G-7,62 - 1708886

Approvals



Drawings

