

Extension adapter - ENLAR-M-KV-M25/M32 - 1647679


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Step-up adapter, M25 to M32, including O-ring



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 947088
GTIN	4017918947088
Weight per Piece (excluding packing)	30.000 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

Dimensions

Length	21 mm
Length without connecting thread	14.5 mm
Connecting thread diameter	25 mm
Hexagon angular dimension	34 mm
Length of the connecting thread	6.5 mm

Ambient conditions

Degree of protection (IP)	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Extension adapter - ENLAR-M-KV-M25/M32 - 1647679

Technical data

General

Material	Brass, nickel-plated
O-ring material	NBR
Outer thread	M25
Internal thread	M32
Color	silver

Standards and Regulations

Halogen-free	no
--------------	----


Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Extension adapter - ENLAR-M-KV-M25/M32 - 1647679

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27439207
eCl@ss 8.0	27439207

Extension adapter - ENLAR-M-KV-M25/M32 - 1647679

Classifications

eCl@ss

eCl@ss 9.0	27430314
------------	----------

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938
ETIM 6.0	EC000938
ETIM 7.0	EC000938

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408