

## Crimp contact - CK4,0-ED-2,50ST AG - 1663242


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Turned 4.0 crimp contact, individual male contact, core diameter 2.50 mm<sup>2</sup>, silver-plated



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 017918 123055
Weight per Piece (excluding packing)	3.16 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Electrical characteristics

Note	For HC-M-3 modules
------	--------------------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Mechanical characteristics

Conductor cross section	2.5 mm <sup>2</sup>
Connection cross section AWG	14
Stripping length of the individual wire	9 mm
Insertion/withdrawal cycles	≥ 500

#### General

Type	Individual male contact
Series	HC-M-03

# Crimp contact - CK4,0-ED-2,50ST AG - 1663242

## Technical data

### General

Connection method	Crimp connection
-------------------	------------------

### Material data

Contact material	Copper alloy
Contact surface material	silver-plated

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

### ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Approvals

### Approvals

---

Approvals

EAC / EAC

---

# Crimp contact - CK4,0-ED-2,50ST AG - 1663242

## Approvals

Ex Approvals

---

Approvals submitted

---

Approval details

EAC

EAC

## Drawings

Dimensional drawing

