

## Protective covers - HC-B 16-TMS-SD-IP50 - 1690752

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Protective cover B16, Clip locking, protective cover material: PA, height: 31.2 mm, seal: no, With lanyard, diameter of retaining cord eyelet: 4 mm

RoHS

COMPLETE

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 890643
GTIN	4017918890643
Weight per Piece (excluding packing)	39.720 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Length	124 mm
Width	55 mm
Height	31.2 mm
Diameter of retaining cord eyelet	3.5 mm

#### Ambient conditions

Degree of protection (IP)	IP50
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	B16
------	-----

## Protective covers - HC-B 16-TMS-SD-IP50 - 1690752

### Technical data

#### General

Type	HC-ADVANCE protective cover
Material	PA
Flammability rating according to UL 94	V0
Color	gray
Seal present	no

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

#### ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

#### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421

## Protective covers - HC-B 16-TMS-SD-IP50 - 1690752

### Approvals

Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

---