

## Printed-circuit board connector - PC 4/ 8-G-7,62 BK - 1729726

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 20 A, Number of positions: 8, Pitch: 7.62 mm, Color: black, Contact surface: Tin, Mounting: Wave soldering



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	16.71 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Dimensions

Pitch	7.62 mm
Dimension a	53.34 mm
Constructional height	15 mm
Length of the solder pin	5 mm

#### General

Range of articles	PC 4/..-G
Rated voltage (III/3)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I <sub>N</sub>	20 A
Color	black
Number of positions	8

#### Standards and Regulations

Connection in acc. with standard	EN-VDE
	CSA

# Printed-circuit board connector - PC 4/ 8-G-7,62 BK - 1729726

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

CSA / UL Recognized / cUL Recognized / LR / GL / DNV / RS / EAC / EAC / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted


---


#### Approval details

# Printed-circuit board connector - PC 4/ 8-G-7,62 BK - 1729726

## Approvals

CSA 

UL Recognized 

cUL Recognized 

LR

GL

DNV

RS

EAC

EAC

cULus Recognized 