

Printed-circuit board connector - GMSTBV 2,5/ 3-GF-7,62 EX - 1796678

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Nominal current (Ex): 12 A, Nominal voltage (Ex): 352 V, Number of positions: 2, Pitch: 7.62 mm, Color: green, Contact surface: Tin, Mounting: Wave soldering



Product Features

- Ex approval for voltages up to 275 V



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	2.8 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Pitch	7.62 mm
Dimension a	15.24 mm
Constructional height	12 mm
Pin dimensions	1 x 1 mm
Hole diameter	1.4 mm

General

Range of articles	GMSTBV 2,5/...-GF-EX
Insulating material group	I
Rated voltage (III/3)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A
Insulating material	PA

Printed-circuit board connector - GMSTBV 2,5/ 3-GF-7,62 EX - 1796678

Technical data

General

Flammability rating according to UL 94	V0
Color	green
Number of positions	2

Ex-specific data

Identification	0344# II 2GD Ex e IIC Gb
EU type-examination certificate	KEMA 10ATEX0196 U
IECEX certificate	IECEX KEM 10.0093U
Rated voltage	352 V
Rated current	12 A

Standards and Regulations

Connection in acc. with standard	EN-VDE
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Printed-circuit board connector - GMSTBV 2,5/ 3-GF-7,62 EX - 1796678

Approvals

Approvals

Approvals

EAC

Ex Approvals

IECEX / ATEX / EAC Ex


Approvals submitted

Approval details

EAC

Drawings

Drilling diagram



Dimensional drawing

