

## Housing - HC-B 32-TFQ-80/M1PG21G - 1775677

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for double locking latch, height 80 mm, with screw connection, 1x Pg21, straight cable entry



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 038243
Weight per Piece (excluding packing)	460.0 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	80 mm
Width	79 mm
Length	94 mm
Wrench size, union nut	28 mm
External cable diameter	10 mm ... 19 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B32, DD144, M
Size	B32
Housing type	Sleeve housing

# Housing - HC-B 32-TFQ-80/M1PG21G - 1775677

## Technical data

### General

Locking type	For double locking latch
No. of cable outlets	1
Cable exit	straight
Screw connection	with
Type of the screw connection	1x Pg21
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

# Housing - HC-B 32-TFQ-80/M1PG21G - 1775677

## Approvals

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

## Approval details

EAC
-----

## Drawings

Dimensional drawing

