

Base strip - MSTBO 2,5/ 8-GL-5,08 - 1850495

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 8 A, Rated voltage (III/2): 320 V, Number of positions: 8, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Mounting: Wave soldering

Product Features

- Header perpendicular (orthogonal) to the PCB
- PCB is to the left of the header
- Space-saving header



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 102920
Weight per Piece (excluding packing)	8.51 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Length	59.3 mm
Pitch	5.08 mm
Dimension a	35.56 mm
Constructional height	9 mm
Length of the solder pin	3.2 mm
Pin dimensions	1,2 x 0,32 mm
Hole diameter	1.3 mm

Base strip - MSTBO 2,5/ 8-GL-5,08 - 1850495

Technical data

General

Range of articles	MSTBO 2,5/..-GL
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	630 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	8 A
Maximum load current	8 A
Insulating material	PA
Flammability rating according to UL 94	V0
Color	green
Number of positions	8

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CSA
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

Base strip - MSTBO 2,5/ 8-GL-5,08 - 1850495

Classifications

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCE CB Scheme / EAC / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA			
	B	D	
	Nominal current IN	6.5 A	6.5 A
	Nominal voltage UN	300 V	300 V

UL Recognized			
	B	D	
	Nominal current IN	8 A	8 A
	Nominal voltage UN	250 V	300 V

Base strip - MSTBO 2,5/ 8-GL-5,08 - 1850495

Approvals

VDE Gutachten mit Fertigungsüberwachung	
Nominal current IN	8 A
Nominal voltage UN	250 V

cUL Recognized		
	B	D
Nominal current IN	8 A	8 A
Nominal voltage UN	250 V	300 V

IECEE CB Scheme	
Nominal current IN	8 A
Nominal voltage UN	250 V

EAC


EAC

cULus Recognized	
------------------	--

Drawings

Base strip - MSTBO 2,5/ 8-GL-5,08 - 1850495

Drilling diagram



Dimensional drawing

