

## Protective covers - VC-SD2 - 1853683

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOCON dust cover for panel mounting frame, with IP40 protection, type 2

### Your advantages

- Easy mounting
- Contact inserts are protected when not plugged in

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| Minimum order quantity               | 5 pc  |
| GTIN                                 | <br>4 017918 145903 |
| GTIN                                 | 4017918145903   |
| Weight per Piece (excluding packing) | 12.220 g  |
| Custom tariff number                 | 39269097  |
| Country of origin                    | Poland  |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Width  | 71.5 mm |
| Height | 31 mm   |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

#### General

|      |     |
|------|-----|
| Size | VC2 |
|------|-----|

## Protective covers - VC-SD2 - 1853683

### Technical data

#### General

|  |                           |
|--|---------------------------|
| Type                                   | For panel mounting frames |
| Material                               | PA                        |
| Flammability rating according to UL 94 | V0                        |
| Seal present                           | no                        |
| Mounting type                          | Clip locking              |

#### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.1 | 27142100 |
| eCl@ss 6.0 | 27261200 |
| eCl@ss 7.0 | 27440208 |
| eCl@ss 8.0 | 27440208 |
| eCl@ss 9.0 | 27440208 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000241 |
| ETIM 3.0 | EC002040 |
| ETIM 4.0 | EC002040 |
| ETIM 5.0 | EC002314 |
| ETIM 6.0 | EC002314 |
| ETIM 7.0 | EC002314 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212113 |
| UNSPSC 7.0901 | 39121712 |
| UNSPSC 11     | 39121712 |
| UNSPSC 12.01  | 39121712 |
| UNSPSC 13.2   | 39121421 |