

Cable gland - VC-EMV-KV-PG16(9-13/10,5) - 1854174

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



EMC half screw connection Pg16, for metal housings, consisting of rubber seal, iris spring, cone disks and pressure screw, for size 1 housings, cable shielding range [mm] 6.5-10.5, cable [mm] 9-13

The figure shows versions Pg16 and Pg21



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4017918145767

Technical data

Dimensions

Wrench size, union nut	24 mm
External cable diameter	9 mm ... 13 mm
Shield diameter	10.5 mm

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
No. of conductors	1
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Sealing material	TPE
Shielded	yes
Thread type on seal side	Pg16
Tightening torque, union nut	7.50 Nm

Cable gland - VC-EMV-KV-PG16(9-13/10,5) - 1854174

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>