

# Printed-circuit board connector - PC 4/10-G-7,62 BK - 1927056

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB headers, nominal current: 20 A, number of positions: 10, pitch: 7.62 mm, color: black, contact surface: Tin, mounting: Wave soldering


The figure shows a 5-pos. version of the product

## Why buy this product

- Well-known mounting principle allows worldwide use



## Key Commercial Data

Packing unit	50 STK
GTIN	 4 017918 611835
GTIN	4017918611835

## Technical data

### Dimensions

Pitch	7.62 mm
Dimension a	68.58 mm
Constructional height	15 mm
Length of the solder pin	5 mm

### General

Range of articles	PC 4/..-G
Rated voltage (III/3)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I <sub>N</sub>	20 A
Color	black
Number of positions	10

## Standards and Regulations

Connection in acc. with standard	EN-VDE
----------------------------------	--------

# Printed-circuit board connector - PC 4/10-G-7,62 BK - 1927056

## Technical data

### Standards and Regulations

	CSA
--	-----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Approvals

### Approvals


#### Approvals


CSA / EAC / cULus Recognized

#### Ex Approvals

### Approval details

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	13631
	B	C	
Nominal current I <sub>N</sub>	20 A	20 A	
Nominal voltage U <sub>N</sub>	300 V	300 V	

EAC			B.01742
-----	---	--	---------

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E60425-19920722
	B	C	
Nominal current I <sub>N</sub>	20 A	20 A	
Nominal voltage U <sub>N</sub>	300 V	300 V	

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>