

Base strip - MCO 1,5/10-GR-3,81 - 1861727


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 8 A, Rated voltage (III/2): 160 V, Number of positions: 10, Pitch: 3.81 mm, Color: green, Contact surface: Tin, Mounting: Wave soldering

Product Features

- Pin strip perpendicular (orthogonal) to the PCB
- PCB is to the right of the header
- Pitch: 3.81 mm
- Space-saving header



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	7.47 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Length	52.29 mm
Pitch	3.81 mm
Dimension a	34.29 mm
Constructional height	8 mm
Length of the solder pin	3 mm
Pin dimensions	0,9 x 0,32 mm
Hole diameter	1 mm

General

Range of articles	MCO 1,5/...-GR
-------------------	----------------

Base strip - MCO 1,5/10-GR-3,81 - 1861727

Technical data

General

Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	125 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	200 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	8 A
Insulating material	PA (PBT)
Flammability rating according to UL 94	V0
Color	green
Number of positions	10

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
-------------	----------

Base strip - MCO 1,5/10-GR-3,81 - 1861727

Classifications

UNSPSC

UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCEB CB Scheme / CCA / EAC / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized		
	B	D
Nominal current IN	8 A	8 A
Nominal voltage UN	300 V	300 V

VDE Gutachten mit Fertigungsüberwachung	
Nominal current IN	8 A
Nominal voltage UN	125 V

Base strip - MCO 1,5/10-GR-3,81 - 1861727

Approvals

cUL Recognized

	B	D
Nominal current I_N	8 A	8 A
Nominal voltage U_N	300 V	300 V

IECEE CB Scheme

Nominal current I_N	8 A
Nominal voltage U_N	125 V

CCA

Nominal current I_N	8 A
Nominal voltage U_N	125 V


EAC

EAC

cULus Recognized

Drawings

Drilling diagram



Dimensional drawing

