

DIN rail bus connectors - TBUS8-20,0-PPPPPPPP-7035 - 2202889

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

DIN rail connector, number of positions: 8, pitch: 2.54 mm, color: light gray, 8 parallel contacts



Your advantages

- ✓ Space-saving DIN rail mounting
- ✓ Contact design enables electronics modules to be easily snapped on
- ✓ Power supply and communication without additional wiring
- ✓ Parallel and serial contacts for efficient signal and data transmission



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 055626 382135
GTIN	4055626382135
Weight per Piece (excluding packing)	4.530 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Length [l]	20 mm
Pitch	2.54 mm

General

Number of positions	8
Insulating material group	I
Rated surge voltage (III/2)	1.5 kV
Rated surge voltage (II/2)	1.5 kV
Rated voltage (III/2)	32 V

DIN rail bus connectors - TBUS8-20,0-PPPPPPP-7035 - 2202889

Technical data

General

Rated voltage (II/2)	32 V
Nominal current I _N	6 A
Maximum load current	6 A
Insulating material	PA
Flammability rating according to UL 94	V0

General product information

Type of note	Recommendation
Note	Material of contact pads for bus connector, galvanic gold (hard gold)

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 5.0	EC002638
ETIM 6.0	EC002638
ETIM 7.0	EC002638

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

DIN rail bus connectors - TBUS8-20,0-PPPPPPP-7035 - 2202889

Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20151204
Nominal voltage UN		29.9 V
Nominal current IN		6 A

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20151204
Nominal voltage UN		29.9 V
Nominal current IN		4 A

EAC		B.01687
-----	--	---------

cULus Recognized		
------------------	--	--

Accessories

Additional products

Printed-circuit board connector - FMC 0,5/ 8-ST-2,54 - 1821151

PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.5 mm², number of positions: 8, pitch: 2.54 mm, connection method: Push-in spring connection, color: black, contact surface: Gold

