



SKBI 128-B64/B64

Order No.: 2268028

The illustration shows the version SKBI 128-B 32/B 32

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2268028>Plug-in card block, Number of positions: 128, Pitch: 0 mm, Connection
method: Screw connection

Commercial data

GTIN (EAN)	
sales group	E213
Pack	1 pcs.
Customs tariff	85369010
Catalog page information	Page 556 (CC-2011)

Product notes

WEEE/RoHS-compliant since:
06/07/2006

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions / positions

Length	66 mm
Height	162 mm
Width	252.4 mm
Pitch	0 mm
Number of positions	128

Hole diameter	4.2 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Technical data

Range of articles	SKBI 128
Connection in acc. with standard	EN-VDE
Nominal current I_N	(current values are defined by the plug connectors used)
Nominal voltage U_N	(voltage values are defined by the plug connectors used)
Nominal cross section	2.5 mm ²
Stripping length	8 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;