

Inline terminal - GE-IB IL TEMP 2 RTD - 2855774

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VersaPoint analog input module, complete with accessories (plug and labeling field), 2 inputs, RTD (resistive sensors), 2-, 3-, 4-wire connection method

Product Description

The terminal is designed for use within an Inline station.

It is used to acquire signals from resistive temperature sensors.

The terminal supports all common platinum and nickel sensors according to DIN EN 60751 and SAMA.

Cu10, Cu50, and Cu53 sensors as well as KTY81 and KTY84 sensors are also supported.

The measuring temperature is represented by 16-bit values in two process data words (one word per channel).

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 017918 820534
GTIN	4017918820534
Weight per Piece (excluding packing)	100.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
------------	--

Inline terminal - GE-IB IL TEMP 2 RTD - 2855774

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 10.0.1	27242601
eCl@ss 4.0	27250303
eCl@ss 4.1	27250303
eCl@ss 5.0	27250303
eCl@ss 5.1	27242601
eCl@ss 6.0	27242601
eCl@ss 7.0	27242601
eCl@ss 8.0	27242601
eCl@ss 9.0	27242601

ETIM

ETIM 2.0	EC001431
ETIM 3.0	EC001596
ETIM 4.0	EC001596
ETIM 5.0	EC001596
ETIM 6.0	EC001596

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602