

CABLE-FCN24/2X14/200/OMR-IN

Order No.: 2304254


CABLE-FCN40/4X14/100/OMR-OUT version is illustrated



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2304254>

System cable with 24-pos. Fujitsu strip and two 14-pos. FLK strips for connecting to CS1, C200H (ID 215, MD 115, MD 215), cable length: 2 m

Commercial data

GTIN (EAN)	 4 017918 929794
Note	Made-to-order
sales group	I680
Pack	1 pcs.
Customs tariff	85444290
Catalog page information	Page 223 (IF-2011)

Product notes

WEEE/RoHS-compliant since:
08/23/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A

Max. conductor resistance	0.16 Ω/m
Ambient temperature (operation)	-20 °C ... 50 °C
Number of positions, control side	24
Number of connectors, control side	1
Number of positions, module side	14
Number of connectors, modul side	2
Fixed cable length	2 m
Single wire, cross section	0.14 mm ²
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	6.3 mm
Shielding	no

Certificates / Approvals



Certification

CUL, UL

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;