

## Cable - FLK 16/14/DV-IN/400 - 2305185

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Round cable set; controller: Emerson Delta V; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 4 m

### Why buy this product

- The DeltaV system can be used to install the process wiring via "mass termination blocks" (MTBs) using flat-ribbon cable plugs
- For digital modules with 16-pos. MTB for connection to PLC-INTERFACE



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 038904
GTIN	4046356038904

### Technical data

#### General

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega$ /m
Length of cable	4 m
Single wire, cross section	0.14 mm <sup>2</sup>
Single wire, cross section [AWG]	26
Single wire, material	Cu tin-plated
External diameter	7 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

#### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

# Cable - FLK 16/14/DV-IN/400 - 2305185

## Technical data

### Environmental conditions

Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

### Connector 1

Connection name	Field level
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	14
Pitch	2.54 mm

### Connector 2

Connection name	Controller level
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

### Supported controller

Controller	Emerson DeltaV
- suitable I/O card	VE4001S2T1B3
	VE4001S2T2B3

### Standards and Regulations

Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

### Color code

Connector 1 = connector 2 (optional) = wire color	IDC/FLK16 (1) = IDC/FLK14 (1) = black
	IDC/FLK16 (2) = IDC/FLK14 (9) = brown
	IDC/FLK16 (3) = IDC/FLK14 (2) = red
	IDC/FLK16 (4) = IDC/FLK14 (9) = orange
	IDC/FLK16 (5) = IDC/FLK14 (3) = yellow
	IDC/FLK16 (6) = IDC/FLK14 (9) = green
	IDC/FLK16 (7) = IDC/FLK14 (4) = blue
	IDC/FLK16 (8) = IDC/FLK14 (11) = violet
	IDC/FLK16 (9) = IDC/FLK14 (5) = gray
	IDC/FLK16 (10) = IDC/FLK14 (11) = white
	IDC/FLK16 (11) = IDC/FLK14 (6) = white-black
	IDC/FLK16 (12) = IDC/FLK14 (11) = white-brown
	IDC/FLK16 (13) = IDC/FLK14 (7) = white-red
	IDC/FLK16 (14) = IDC/FLK14 (13) = white-orange
	IDC/FLK16 (15) = IDC/FLK14 (8) = white-yellow
	IDC/FLK16 (16) = IDC/FLK14 (13) = white-green

# Cable - FLK 16/14/DV-IN/400 - 2305185

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

#### Approvals

EAC / UL Listed / cUL Listed / cULus Listed

#### Ex Approvals

### Approval details

EAC		RU C-DE.A*30.B00767
-----	--	---------------------

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cULus Listed	
--------------	--

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>