

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 2.5 m



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 099738
GTIN	4046356099738
Weight per Piece (excluding packing)	400.000 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m
Length of cable	2.5 m
Single wire, cross section	0.14 mm ²
Single wire, cross section [AWG]	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	10.3 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Technical data

General

Shielding	no
Insertion/withdrawal cycles	> 50

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-3
	DIN VDE 0482 Part 266-2

Connector 1

Connection name	Field level
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Connector 2

Connection name	Controller level
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Supported controller

Controller	SIEMENS S7-300 / ET 200 M
- suitable I/O card	CPU 313C-2DP
	CPU 314C-2PtP
	6ES7 321-1BL00-0AA0
	6ES7 322-1BL00-0AA0
	6ES7 323-1BL00-0AA0
	6ES7 331-7NF00-0AB0
	6ES7 331-7PF01-0AB0
	6ES7 331-7PF11-0AB0
	6ES7 350-2AH01-0AE0
	6ES7 357-4AH01-0AE0
	CPU 314C-2DP
	6ES7 332-5HF00-0AB0
	6ES7 331-7NF10-0AB0
	6ES7 331-1KF01-0AB0

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Technical data

Supported controller

	CPU 313C
	CPU 313C-2PiP
Controller	SIEMENS S7-400
- suitable I/O card	6ES7 421-1BL01-0AA0
	6ES7 421-7BH01-0AB0
	6ES7 421-7DH00-0AA0
	6ES7 422-1BL00-0AA0
	6ES7 422-7BL00-0AB0
	6ES7 431-0HH0-0AB0
	6ES7 431-1KF00-0AB0
	6ES7 431-1KF10-0AB0
	6ES7 431-1KF20-0AB0
	6ES7 431-7KF00-0AB0
	6ES7 431-7KF10-0AB0
	6ES7 431-7QH00-0AB0
	6ES7 432-1HF00-0AB0
Controller	Schneider Electric Modicon TSX QUANTUM
- suitable I/O card	DDI 353
	DDI 841
	DDI 853
	DAI 340
	DAI 353
	DAI 440
	DAI 453
	DDO 353
	DDM 390
	ACI 030
	ACI 040
	ATI 030
	ARI 030
	AVI 030
	ACO 020
	ACO 130
	AVO 020
	EHC 105
	EHC 202
Controller	ALLEN-BRADLEY ControlLogix

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Technical data

Supported controller

- suitable I/O card	1756-IA16I
	1756-IB16D
	1756-IB16I
	1756-IB32
	1756-IH16I
	1756-OB32
	1756-IF8
	1756-IF16
	1756-HSC
	1756-M02AE
Controller	ALLEN-BRADLEY PLC 5
- suitable I/O card	1771 IBN
	1771 OBN
Controller	HONEYWELL Experion PKS C200
- suitable I/O card	TC-IDK 161
	TC-IDX 161
	TC-IDJ 161
	TC-IDD 321
	TC-ODD 321
	TC-IAH 161
Controller	ALLEN-BRADLEY SLC 500
- suitable I/O card	1746 OA16
	1746 OW16

Standards and Regulations

Flame resistance	IEC 60332-3
	DIN VDE 0482 Part 266-2

Color code

Connector 1 = connector 2 (optional) = wire color	IDC/FLK50 (1) = IDC/FLK50 (1) = black
	IDC/FLK50 (2) = IDC/FLK50 (2) = brown
	IDC/FLK50 (3) = IDC/FLK50 (3) = red
	IDC/FLK50 (4) = IDC/FLK50 (4) = orange
	IDC/FLK50 (5) = IDC/FLK50 (5) = yellow
	IDC/FLK50 (6) = IDC/FLK50 (6) = green
	IDC/FLK50 (7) = IDC/FLK50 (7) = blue
	IDC/FLK50 (8) = IDC/FLK50 (8) = violet
	IDC/FLK50 (9) = IDC/FLK50 (9) = gray

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Technical data

Color code

	IDC/FLK50 (10) = IDC/FLK50 (10) = white
	IDC/FLK50 (11) = IDC/FLK50 (11) = white-black
	IDC/FLK50 (12) = IDC/FLK50 (12) = white-brown
	IDC/FLK50 (13) = IDC/FLK50 (13) = white-red
	IDC/FLK50 (14) = IDC/FLK50 (14) = white-orange
	IDC/FLK50 (15) = IDC/FLK50 (15) = white-yellow
	IDC/FLK50 (16) = IDC/FLK50 (16) = white-green
	IDC/FLK50 (17) = IDC/FLK50 (17) = white-blue
	IDC/FLK50 (18) = IDC/FLK50 (18) = white-violet
	IDC/FLK50 (19) = IDC/FLK50 (19) = white-gray
	IDC/FLK50 (20) = IDC/FLK50 (20) = brown-black
	IDC/FLK50 (21) = IDC/FLK50 (21) = brown-red
	IDC/FLK50 (22) = IDC/FLK50 (22) = brown-orange
	IDC/FLK50 (23) = IDC/FLK50 (23) = brown-yellow
	IDC/FLK50 (24) = IDC/FLK50 (24) = brown-green
	IDC/FLK50 (25) = IDC/FLK50 (25) = brown-blue
	IDC/FLK50 (26) = IDC/FLK50 (26) = brown-violet
	IDC/FLK50 (27) = IDC/FLK50 (27) = brown-gray
	IDC/FLK50 (28) = IDC/FLK50 (28) = brown-white
	IDC/FLK50 (29) = IDC/FLK50 (29) = green-black
	IDC/FLK50 (30) = IDC/FLK50 (30) = green-brown
	IDC/FLK50 (31) = IDC/FLK50 (31) = green-red
	IDC/FLK50 (32) = IDC/FLK50 (32) = green-orange
	IDC/FLK50 (33) = IDC/FLK50 (33) = green-blue
	IDC/FLK50 (34) = IDC/FLK50 (34) = green-violet
	IDC/FLK50 (35) = IDC/FLK50 (35) = green-gray
	IDC/FLK50 (36) = IDC/FLK50 (36) = green-white
	IDC/FLK50 (37) = IDC/FLK50 (37) = yellow-black
	IDC/FLK50 (38) = IDC/FLK50 (38) = yellow-brown
	IDC/FLK50 (39) = IDC/FLK50 (39) = yellow-red
	IDC/FLK50 (40) = IDC/FLK50 (40) = yellow-orange
	IDC/FLK50 (41) = IDC/FLK50 (41) = yellow-blue
	IDC/FLK50 (42) = IDC/FLK50 (42) = yellow-violet
	IDC/FLK50 (43) = IDC/FLK50 (43) = yellow-gray
	IDC/FLK50 (44) = IDC/FLK50 (44) = yellow-white
	IDC/FLK50 (45) = IDC/FLK50 (45) = gray-black
	IDC/FLK50 (46) = IDC/FLK50 (46) = gray-brown

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Technical data

Color code

	IDC/FLK50 (47) = IDC/FLK50 (47) = gray-red
	IDC/FLK50 (48) = IDC/FLK50 (48) = gray-orange
	IDC/FLK50 (49) = IDC/FLK50 (49) = gray-yellow
	IDC/FLK50 (50) = IDC/FLK50 (50) = gray-green

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.1	27249205
eCl@ss 6.0	27249205
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237
ETIM 6.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Approvals

EAC / UL Listed / cUL Listed / cULus Listed

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176

Approvals

Ex Approvals

Approval details

EAC			RU C-DE.A*30.B00767
-----	--	--	---------------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal current IN	1 A		
Nominal voltage UN	125 V		

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal current IN	1 A		
Nominal voltage UN	125 V		

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

