

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Cast Yokogawa front adapter with attached round cable and an injection-molded 50-pos. socket strip for the connection of 4 x 8 channels on the field side. Cable length: 20.0 m

## Your advantages

- Four 14-pos. connectors on the module side for connecting four 8-channel VARIOFACE modules of the system cabling
- Lateral cable outlet of the I/O module

## Commercial Data

Item number	2314778
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	I1 - Systemverkabelung
Product Key	CK2154
Catalog Page	Page 515 (C-5-2019)
GTIN	4046356167666
Weight per Piece (including packing)	4.115,6 g
Weight per Piece (excluding packing)	3.861,5 g
Customs tariff number	85444290
Country of origin	DE

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

## Technical Data

### Product properties

Product type	Front adapter
--------------	---------------

### Electrical properties

Max. permissible operating voltage	30 V DC
Max. permissible current	500 mA (per path at 70°C)

Supported controller YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV551

Supported controller YOKOGAWA STARDOM

Suitable I/O card	NFDV151
	NFDV551

### Connection data

#### Control side

Connection method	Yokogawa, I/O cards compatible
Number of connections	1
Number of positions	50
Tightening torque	0.5 Nm (Screw connection)

#### Module side

Connection method	IDC/FLK socket strip
Number of connections	4
Number of positions	14
Pitch	2.54 mm

### Dimensions

Length	20 m
--------	------

### Cable / line

Cable length	20 m
--------------	------

#### 50X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	50
Shielded	yes
Cable type	50X0.14 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	50x 0.14 mm <sup>2</sup>

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	11 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	114 mm
Smallest bending radius, movable installation	205 mm
Max. bending cycles	5000 (at a radius of ≥ 18x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Approval data

### UKCA

Certificate	UKCA-compliant
-------------	----------------

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

## Drawings

Connection diagram

50-pos. connector to the I/O card	4 x 14-pos. connector to the module		Wire color
1	Byte 0	1	black
3		2	brown
5		3	red
7		4	orange
9		5	yellow
11		6	green
13		7	blue
15		8	Violet
41		9	gray
39		10	White
17	Byte 1	1	white-black
19		2	white-brown
21		3	white-red
23		4	white-orange
25		5	White-yellow
27		6	white-green
29		7	white-blue
31		8	white-violet
43		9	white-gray
37		10	brown-black
2	Byte 2	1	brown-red
4		2	brown-orange
6		3	brown-yellow
8		4	brown-green
10		5	brown-blue
12		6	brown-violet
14		7	brown-gray
16		8	brown-white
42		9	green-black
36		10	green-brown
18	Byte 3	1	green-red
20		2	green-orange
22		3	green-blue
24		4	green-violet
26		5	green-gray
28		6	green-white
30		7	yellow-black
32		8	yellow-brown
44		9	yellow-red
34		10	yellow-orange

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

## Approvals



### EAC

Approval ID: RU\*-DE.HB\*35.B00385



### UL Listed

Approval ID: FILE E 238705

	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	125 V	0.5 A	-	-



### cUL Listed

Approval ID: FILE E 238705

	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	125 V	0.5 A	-	-

### cULus Listed

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

## Classifications

### ECLASS

ECLASS-9.0	27242292
ECLASS-10.0.1	27242292
ECLASS-11.0	27242292

### ETIM

ETIM 8.0	EC002584
----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# Front adapters - CABLE-50/4FLK14/20,0M/YUC



2314778

<https://www.phoenixcontact.com/de/produkte/2314778>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# Front adapters - CABLE-50/4FLK14/20,0M/YUC

2314778

<https://www.phoenixcontact.com/de/produkte/2314778>



## Accessories

### Cable marker carrier

Cable marker carrier - KME - 0807083

<https://www.phoenixcontact.com/de/produkte/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH

Flachmarktstraße 8

D-32825 Blomberg

+49 52 35/3-1 20 00

[info@phoenixcontact.de](mailto:info@phoenixcontact.de)