

## Front adapters - FLKM-PA-D25/HW/AID16/C300 - 2905198

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE front adapter, for Honeywell C300, series I/O, includes 16 differential signals (D1-D16) and 25-pos. D-SUB connector

### Why buy this product

- Pre-assembled system cables are connected directly to I/O modules using the front adapters
- Front adapter with D-SUB connector
- Connection of analog modules

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 002989
GTIN	4055626002989
Weight per Piece (excluding packing)	650.000 g
Custom tariff number	85366990
Country of origin	United States

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)

# Front adapters - FLKM-PA-D25/HW/AID16/C300 - 2905198

## Technical data

### General

Mounting position	any
-------------------	-----

### Connection data 1

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	25

### Supported controller


Controller	HONEYWELL Experion PKS C300/C-Series
- suitable I/O card	TAID01
	TAIDA1

### Standards and Regulations

Standards/regulations	DIN EN 50178
	IEC 60664
Degree of pollution	2
Overvoltage category	II

## Drawings

Circuit diagram



# Front adapters - FLKM-PA-D25/HW/AID16/C300 - 2905198

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / cULus Recognized

---

#### Ex Approvals

---

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
mm <sup>2</sup> /AWG/kcmil		30-12	
Nominal current I <sub>N</sub>		1 A	
Nominal voltage U <sub>N</sub>		125 V	

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
mm <sup>2</sup> /AWG/kcmil		30-12	
Nominal current I <sub>N</sub>		1 A	
Nominal voltage U <sub>N</sub>		125 V	

cULus Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	
------------------	--	---	--