

## Electronic housing - EMG 17-LG/SET - 2942988

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Electronic housing set, consisting of electronic housing and printed circuit termination blocks, pitch 5

### Your advantages

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ Uniform and appropriate housing technology
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 080945
GTIN	4017918080945
Weight per Piece (excluding packing)	33.700 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### General

## Electronic housing - EMG 17-LG/SET - 2942988

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color (RAL)	green

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Dimensions

Length	75 mm
Height	47.5 mm
Width	17.5 mm
Pitch	5 mm
Depth	75 mm

#### Technical data

Power dissipation without gap	1.3 W
Power dissipation with 20 mm gap	1.4 W
Number of positions	6

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings


# Electronic housing - EMG 17-LG/SET - 2942988

Dimensional drawing



1 = Top edge of the PCB  
B = Housing width

Dimensional drawing



Pitch 5 mm  
a = Area for mounting components, 38 mm in the hood

## Electronic housing - EMG 17-LG/SET - 2942988

b = Area for mounting components, 45 mm in the housing

### Articles in set

Electronic housing - EMG 17-LG - 2946078



Electronic housing, with universal foot, for p.c.b. insertion, without screw connection terminal blocks and cover, pitch 5

Electronic housing - EMG 17-LG-7,5 - 2944106



Electronic housing, with universal foot, for p.c.b. insertion, without screw connection terminal blocks and cover, pitch 7.5

Electronic housing - EMG 17-LG/O - 2942409



Electronic housing, with universal foot, for p.c.b. insertion, without screw connection terminal blocks and cover, pitch 5, with open terminal space

PCB terminal block - MKDS 3/ 3 - 1711039



PCB terminal block, nominal current: 24 A, rated voltage (III/2): 400 V, nominal cross section: 2.5 mm<sup>2</sup>, pitch: 5 mm, number of positions: 3, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: green, Pin layout: Linear pinning, Solder pin [P]: 5 mm. The article can be aligned to create different nos. of positions!

### Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500

# Electronic housing - EMG 17-LG/SET - 2942988

## Classifications

### eCl@ss

eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Accessories

### Accessories

#### Filler plug

#### Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

---

### PCB

## Electronic housing - EMG 17-LG/SET - 2942988

### Accessories

PCB - P 1-EMG 17 - 2946120



PCB for assembling electronic components

---

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

### Necessary add-on products

Covering hood - EMG 17-H 7,5MM KLAR - 2946094



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm, width: 17 mm

---

Covering hood - EMG 17-H 15MM KLAR - 2946104



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 17 mm

---

## Electronic housing - EMG 17-LG/SET - 2942988

### Accessories

Electronic housing - EMG 17-H 35MM KLAR - 2942221



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 35 mm, width: 17 mm

---

Covering hood - EMG 17-H 52MM GN - 2946117



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 17.5 mm

---