

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Complete housing, length: 99 mm, without vents, Cross connection: DIN rail bus connector, color: light gray, width: 35 mm, height: 114.5 mm, number of positions cross connector: 5

### Why buy this product

- Item is from the ME-MAX product range
- Easy mounting
- Available in overall widths from 6.2 mm to 90 mm, modular extension is possible
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail
- Optional with bus connector for DIN rail mounting as well as power connection system

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 017918 936082
GTIN	4017918936082
Weight per Piece (excluding packing)	83.500 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Housing type	Complete housing
Housing material	Polyamide

# Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

## Technical data

### General

Color (RAL)	light gray (7035)
-------------	-------------------

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

### Dimensions

Length	99 mm
Constructional height	114.5 mm
Width	35 mm
Depth	99 mm

### Technical data

Connection in acc. with standard	CUL
Indicator1	CUL1
Power dissipation without gap	7.5 W
Power dissipation with 20 mm gap	13.8 W
Number of positions	36

### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0
mandatory product	2278364 MCO 1,5/ 4-G1L-3,5 KMGY

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

# Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

## Classifications

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

#### Approvals

UL Recognized / cUL Recognized / UL Recognized / cULus Recognized

#### Ex Approvals

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	--	---	---------------

cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
----------------	--	---	--------------

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm</a>	FILE E 60425
---------------	--	---	--------------

# Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

## Approvals

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

## Accessories

### Accessories

#### Fiber optics

#### Component housing - HS LC-H-D3/ R1XC1 - 2202313



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

#### Component housing - HS LC-H-5X2/ R1XC1 - 2202314



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

#### Component housing - HS LC-H-D3/ R2XC1-5,08 - 2202315



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

#### Component housing - HS LC-H-D2/ R2XC1-2,54 - 2202316



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

Component housing - HS LC-H-D2/ R2XC2-2,54 - 2202317



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

---

Component housing - HS LC-H-D2/ R2XC5-2,54 - 2202318



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

---

Component housing - HS LC-H-D2/ R2XC10-2,54 - 2202319



Light guides, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), color: transparent

---

### Filler plug

Filler plugs - ME MAX B-17,5 KMGY - 2706959



Filler plug for unoccupied terminal points, color: Light gray

---

### Ground contact

Electronic housing - ME FE-CONTACT - 2908294



Functional earth ground contact, for intermediate elements.

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

---

#### Necessary add-on products

Base strip - MCO 1,5/ 4-G1L-3,5 KMGY - 2278364



Header, nominal current: 8 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 3.5 mm, color: light gray, contact surface: Tin, mounting: Soldering, Article with lateral pin exit

---

Base strip - MCO 1,5/ 4-G1R-3,5 KMGY - 2278377



Header, nominal current: 8 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 3.5 mm, color: light gray, contact surface: Tin, mounting: Soldering, Article with lateral pin exit

---

Base strip - MSTBO 2,5/ 3-G1PL GY7035 - 2200328



Header, nominal current: 16 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: light gray, contact surface: Tin, mounting: Soldering

---

Base strip - MSTBO 2,5/ 3-G1PR GY7035 - 2200329



Header, nominal current: 16 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: light gray, contact surface: Tin, mounting: Soldering

---

Base strip - MSTBO 2,5/ 3 G1L THRR44 BK - 2915216



Header, nominal current: 16 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: black, contact surface: Tin, mounting: Taped SMD/THT/THR components

---

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

Base strip - MSTBO 2,5/ 3 G1R THRR44 BK - 2915229



Header, nominal current: 16 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: black, contact surface: Tin, mounting: Taped SMD/THT/THR components

---

Base strip - MSTBO 2,5/ 3-G1L KMGY - 2853750



Header, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: light gray, contact surface: Tin, mounting: Soldering

---

Base strip - MSTBO 2,5/ 3-G1R KMGY - 2853763



Header, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, color: light gray, contact surface: Tin, mounting: Soldering

---

Printed-circuit board connector - MKDSO 1,5/ 4-L-3,5 KMGY - 2278432



PCB terminal block, nominal current: 8 A, nom. voltage: 160 V, pitch: 3.5 mm, number of positions: 4, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

---

Printed-circuit board connector - MKDSO 1,5/ 4-R-3,5 KMGY - 2278429



PCB terminal block, nominal current: 8 A, nom. voltage: 160 V, pitch: 3.5 mm, number of positions: 4, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

---

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

#### PCB terminal block - MKDSO 2,5/ 3-L KMGY - 2854102



PCB terminal block, nominal current: 24 A, nom. voltage: 400 V, pitch: 5 mm, number of positions: 3, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

---

#### PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092



PCB terminal block, nominal current: 24 A, nom. voltage: 400 V, pitch: 5 mm, number of positions: 3, connection method: Screw connection with tension sleeve, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

---

#### PCB terminal block - MKDSO 2,5 HV/ 2L-7,5 KMGY - 2199676



PCB terminal block, nominal current: 24 A, nom. voltage: 630 V, pitch: 7.5 mm, number of positions: 2, connection method: Screw connection with tension sleeve, mounting: Wave soldering, color: light gray. Article with lateral pin exit

---

#### PCB terminal block - MKDSO 2,5 HV/ 2R-7,5 KMGY - 2199773



PCB terminal block, nominal current: 24 A, nom. voltage: 630 V, pitch: 7.5 mm, number of positions: 2, connection method: Screw connection with tension sleeve, mounting: Wave soldering, color: light gray. Article with lateral pin exit

---

#### PCB terminal block - FKDSO 2,5/ 3-L KMGY - 2200318



PCB terminal block, nominal current: 22 A, nom. voltage: 250 V, pitch: 5 mm, number of positions: 3, connection method: Push-in spring connection, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

PCB terminal block - FKDSO 2,5/ 3-R KMGY - 2200317



PCB terminal block, nominal current: 22 A, nom. voltage: 250 V, pitch: 5 mm, number of positions: 3, connection method: Push-in spring connection, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: light gray. Article with lateral pin exit

---

### Additional products

Electronic housing - ME 17,5 TBUS 1,5/ 5-ST-3,81 KMGY - 2713645



Plug component, nominal current: 8 A, number of positions: 5, pitch: 3.81 mm

---

Electronic housing - ME 17,5 TBUS 1,5/4P1S KMGY - 2201731



DIN rail connector for ME and ME-MAX, design width: 17.5 mm, 4 parallel positions and 1 serial position, color: light gray (similar to RAL 7035)

---

Electronic housing - ME 17,5 TBUS ADAPTER KMGY - 2201757



DIN rail bus adapter for ME and ME-MAX, design width: 17.5 mm, 5 parallel positions, color: light gray (similar to RAL 7035)

---

Electronic housing - PCO 17,5-L KMGY - 2201684



Power connector for ME-MAX housing, design width: 17.5 mm, 2 positions; used to transmit a total current of up to 42 A at 60 V DC.

## Electronic housing - ME MAX 35 G 3-3 KMGY - 2713544

### Accessories

Electronic housing - ME MAX TBUS BS KMGY - 2199650

Component housing, color: light gray

