


EMG 10-B2

Order No.: 2947750



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2947750>

Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB

Commercial data	
GTIN (EAN)	 4 017918 082864
sales group	F001
Pack	10 pcs.
Customs tariff	85369010
Catalog page information	Page 568 (CC-2011)

Product notes

WEEE/RoHS-compliant since:
08/11/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color	green

Dimensions / positions

Length	75 mm
Width	10 mm
Number of positions	4
Pitch	5 mm

Technical data

Ambient temperature (operation)	-40 °C ... 125 °C
Inflammability class acc. to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	0.9 W 1.2 W 7.5 mm
	1 W 1.4 W 15 mm
	1.5 W 2.2 W 52 mm

Accessories


Item	Designation	Description
Assembly		
2941510	EMG-KA	Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.
Marking		
2947585	EMG-SGKS 10	Equipment marker, narrow

Additional products


Item	Designation	Description
Assembly		
2947763	EMG 10-H 7,5MM KLAR	Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm
2947776	EMG 10-H 15MM KLAR	Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 10 mm
2947789	EMG 10-H 52MM GN	Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 10 mm

Diagrams/Drawings

Dimensioned drawing



1 = Top edge of the PCB
 B = Housing width



Pitch 5 mm
 a = Area for mounting components, 38 mm in the hood
 b = Area for mounting components, 45 mm in the housing

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2011 Phoenix Contact
Technical modifications reserved;