

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Safety-related digital input module, IP20 protection, for the SafetyBridge, INTERBUS-Safety, and PROFIsafe system. The module has 4 safe digital inputs for two-channel assignment or 8 safe digital inputs for single-channel assignment.

Product Description


The safety module is an input module from the Inline product range designed for use at any point within a SafetyBridge, INTERBUS-Safety or PROFIsafe system. The transmission speed of the safety module can be set to 500 kBaud or 2 Mbaud using a switch. One transmission speed must be used consistently within a station. The module has four safe digital inputs for two-channel assignment or eight digital inputs for single-channel assignment.

Your advantages

- SIL 3 according to IEC 61508/EN 61508
- SILCL 3 according to EN 62061
- PL e according to EN ISO 13849-1



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 131582
GTIN	4046356131582
Weight per Piece (excluding packing)	340.000 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Technical data

Dimensions

Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Degree of protection	IP20

Interfaces

Designation	Inline local bus
No. of channels	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

Digital inputs

Input name	Digital inputs
Description of the input	IEC 61131-2 type 3
Connection method	Spring-cage connection
Connection technology	2, 3, 4-wire
Number of inputs	4 (with two-channel assignment) 8 (for single-channel assignment)
Typical response time	See technical data
Input voltage	24 V DC (via clock outputs UT1 and UT2 or external supply)
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Input voltage range	-3 V DC ... 30 V DC
Typical input current per channel	4.2 mA (at 24 V)

Power supply for module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC

General

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Technical data

General

Mounting type	DIN rail
Net weight	349.4 g
Note on weight specifications	with connectors

Inline potentials

Designation	Communications power (U_L)
Supply voltage	7.5 V DC (see safety data)
Current consumption	max. 180 mA
Designation	Main circuit supply (U_M)
Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current consumption	typ. 25 mA (plus current consumption of the inputs when supplied via the clock outputs, plus current consumption of the connected initiators when via through the clock outputs)
	max. 825 mA (see safety data)
Designation	Segment circuit supply (U_S)

Safety-related characteristic data

Designation	IEC 61508 - High demand
Safety Integrity Level (SIL)	max. 3 (two channel; dependent in parameterization and wiring)
Designation	IEC 61508 - Low demand
Safety Integrity Level (SIL)	max. 3 (two channel; dependent in parameterization and wiring)
Designation	EN ISO 13849
Performance level (PL)	max. e (two channel; dependent in parameterization and wiring)
Category	max. 4 (two channel; dependent in parameterization and wiring)
Designation	EN 62061
Safety Integrity Level Claim Limit (SIL CL)	max. 3 (two channel; dependent in parameterization and wiring)

Standards and Regulations

Protection class	III, IEC 61140, EN 61140, VDE 0140-1
------------------	--------------------------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27240400
------------	----------

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Classifications

eCl@ss

eCl@ss 4.1	27240400
eCl@ss 5.0	27250600
eCl@ss 5.1	27242900
eCl@ss 6.0	27242600
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604
eCl@ss 9.0	27242604

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001617
ETIM 4.0	EC001599
ETIM 5.0	EC001599
ETIM 6.0	EC001599
ETIM 7.0	EC001599

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602

Approvals


Approvals

Approvals

Functional Safety / Functional Safety / UL Listed / cUL Listed / PROFIsafe / Functional Safety / PROFIsafe / cULus Listed

Ex Approvals

Approval details

Functional Safety		968/EZ 424.05/17
-------------------	---	------------------

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Approvals

Functional Safety		968/EZ 650.02/17
-------------------	--	------------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
------------	--	---	---------------

PROFIsafe		Z20079
-----------	--	--------

Functional Safety		968/EZ 424.05/17
-------------------	--	------------------

PROFIsafe		Z20206
-----------	--	--------

cULus Listed		
--------------	--	--

Accessories

Accessories

Connector set

Connector set - IB IL 24 SDI 8-PLSET/CP - 2916930



Connector set (yellow), color coded, for safe SDI boards.

Labeling panel

Safety module - IB IL 24 PSDI 8-PAC - 2985688

Accessories

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Labeling field - IB IL FIELD 8 - 2727515

Labeling field, width: 48.8 mm



Terminal marking

Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, mounting type: insert, lettering field size: 62 x 10 mm, Number of individual labels: 72



Insert strip - ESL 62X46 - 0809502

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, mounting type: insert, lettering field size: 62 x 46 mm, Number of individual labels: 120

