

## Inline terminal - IB IL EX-IS DIO 4/NAM-PAC - 2869911

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Inline intrinsically safe digital I/O terminal, 4 configurable input/output channels, complete with accessories

### Why buy this product

- NAMUR sensors supported (EN 60947-5-6)
- 4 configurable I/O channels
- Single-channel diagnostics
- 8.2 V sensor supply



### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	250.000 g
Custom tariff number	85389099
Country of origin	United States

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

# Inline terminal - IB IL EX-IS DIO 4/NAM-PAC - 2869911

## Technical data

### Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Degree of protection	IP20

### General

Mounting type	DIN rail
Net weight	204 g

### Interfaces

Designation	Inline local bus
Connection method	Inline data jumper
Transmission speed	500 kbps

### Inline potentials

Designation	Communications power $U_L$
Supply voltage	5 V DC (via voltage jumper)
Current consumption	max. 50 mA
Supply voltage	28 V DC
Current consumption	max. 190 mA
Power consumption	4.8 W (per channel)

### Digital inputs

Input name	Digital inputs
Description of the input	Can be configured as input or output
Connection method	Inline connector
Connection technology	2-wire
Number of inputs	4
Type of protection	Polarity protection, surge protection

### Digital outputs

Output name	Digital outputs
Output description	Digital passive output
Connection method	Inline connector
Connection technology	3-conductor
Number of outputs	4
Type of protection	Polarity protection, surge protection
Output voltage	24 V
Nominal output voltage	24 V DC

### Standards and Regulations

# Inline terminal - IB IL EX-IS DIO 4/NAM-PAC - 2869911

## Technical data

### Standards and Regulations


Group	IIC (A, B)
	IIB, [IIIC, IIIB] (C, E, F, G)
	IIA (D)
	IIC (A, B)
	IIB, [IIIC, IIIB] (C, E, F, G)
	IIA (D)
ATEX	# II 3(1)GD Ex nA [ia Ga Da] IIC T4 Gc Sira 09ATEX2339X
IECEX	Ex nA [ia Ga Da] IIC T4 Gc IECEX SIR 10.0033X
UL, USA/Canada	Class I, Div. 2, Groups A, B, C, D
Protection class	III, IEC 61140, EN 61140, VDE 0140-1

### Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Connection diagram



Dimensional drawing



## Classifications

eCl@ss

eCl@ss 4.0	27240404
eCl@ss 4.1	27240404
eCl@ss 5.0	27242204
eCl@ss 5.1	27242604
eCl@ss 6.0	27242604
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604

## Inline terminal - IB IL EX-IS DIO 4/NAM-PAC - 2869911

### Classifications

#### eCl@ss

eCl@ss 9.0	27242604
------------	----------

#### ETIM

ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599
ETIM 6.0	EC001599

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602