

## Electronic housing - UM108-PROFIL 235CM BK - 2909963

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Drawn section panel mounting base, with a constructional width of 108 mm and a fixed length of 235 cm

The illustration shows the version UM 45-Profil CM, in green



### Key Commercial Data

Packing unit	1 M
Weight per Piece (excluding packing)	1000.0 g
Custom tariff number	39162000
Country of origin	Germany

### Technical data

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Classifications

#### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

#### ETIM

ETIM 2.0	EC001031
----------	----------

## Electronic housing - UM108-PROFIL 235CM BK - 2909963

### Classifications

#### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

### Drawings

Dimensional drawing

