

## Electronic housing - EMG 12-H 52MM GN - 2947129

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 12.5 mm

RoHS

### Key Commercial Data

Packing unit	10 pc
GTIN	
GTIN	4017918082598

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced PC-F
Color (RAL)	green

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Dimensions

Length	38 mm
Height	52 mm
Width	12.5 mm
Depth	75 mm

#### Technical data

Number of positions	4
---------------------	---

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

## Electronic housing - EMG 12-H 52MM GN - 2947129

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

---

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>