

## Fuse plug - P-FU 6,3X32 LA 250-EX - 3046525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, nominal current: 10 A, width: 8.2 mm, fuse type: G / 6,3 x 32, color: black

### Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection

RoHS



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 919272
GTIN	4046356919272
Weight per Piece (excluding packing)	6.000 g
Custom tariff number	85369095
Country of origin	Poland

### Technical data

#### General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0

# Fuse plug - P-FU 6,3X32 LA 250-EX - 3046525

## Technical data

### Dimensions

Width	8.2 mm
Length	40 mm

### General

Fuse	G / 6,3 x 32
Degree of pollution	3
LED voltage range	110 V AC/DC ... 250 V AC/DC
LED current range	0.41 mA ... 0.96 mA
Maximum load current	10 A (the current is determined by the fuse used)
Nominal current I <sub>N</sub>	10 A (the current is determined by the fuse used)

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27141149
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141149
eCl@ss 8.0	27141149
eCl@ss 9.0	27141149

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000899
ETIM 5.0	EC002018
ETIM 6.0	EC002018
ETIM 7.0	EC002018

# Fuse plug - P-FU 6,3X32 LA 250-EX - 3046525

## Classifications

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121409
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

IECEX / UL Recognized / cUL Recognized / cULus Recognized

---

### Approval details

EAC		RU C- DE.BL08.B.00714
-----	---	--------------------------

---