

Connection element - HV M6/1-VS 2 - 3049262


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Connection element, length: 91.3 mm, width: 42.8 mm, height: 11.4 mm, number of positions: 2, color: silver



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 313568
GTIN	4046356313568
Weight per Piece (excluding packing)	14.800 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Technical data

Color	silver
Material	Copper
Number of positions	2
Length	91.3 mm
Height	11.4 mm
Width	42.8 mm
Hole diameter	6.6 mm
Drill hole spacing	18 mm
Maximum load current	125 A

Environmental Product Compliance

Connection element - HV M6/1-VS 2 - 3049262

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.1	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 3.0	EC000483
ETIM 4.0	EC000483
ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

UNSPSC

UNSPSC 6.01	30211827
UNSPSC 7.0901	39121424
UNSPSC 11	39121424
UNSPSC 12.01	39121424
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC

Ex Approvals

Connection element - HV M6/1-VS 2 - 3049262

Approvals

Approval details

EAC



RU C-
DE.A*30.B.01742