

Fuse plug - P-FU 5X20 LED 24-5 120KOHM - 3209240

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fuse plug, nominal current: 6.3 A, nom. voltage: 250 V, fuse type: G / 5 x 20, color: black

Your advantages

- Large-surface labeling option



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 773478
GTIN	4046356773478
Custom tariff number	85369095
Country of origin	China

Technical data

General

Note	Suitable for terminal blocks with a width of 5.2 mm and above with TG zone
	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0
Degree of pollution	3
LED voltage range	12 V DC ... 30 V DC

Fuse plug - P-FU 5X20 LED 24-5 120KOHM - 3209240

Technical data

General

LED current range	0.35 mA ... 0.95 mA
Maximum load current	6.3 A (the current is determined by the fuse used)
Nominal current I_N	6.3 A (the current is determined by the fuse used)
Nominal voltage U_N	250 V (The current is determined by the fuse used, the voltage by the fuse or selected LED display.)
Fuse	G / 5 x 20
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Ambient conditions

Operating temperature	-60 °C ... 105 °C (max. short-term operating temperature 130°C)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Circuit diagram



Fuse plug - P-FU 5X20 LED 24-5 120KOHM - 3209240

Classifications

eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 11.0	27142001
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 9.0	27142001

ETIM

ETIM 3.0	EC002018
ETIM 4.0	EC002018
ETIM 6.0	EC000035
ETIM 7.0	EC000035

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

Approvals

Approvals

Approvals


CSA / EAC / UL Recognized / cUL Recognized / cULus Recognized


Ex Approvals


Fuse plug - P-FU 5X20 LED 24-5 120KOHM - 3209240


Approvals


Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	13631
Nominal voltage UN		300 V	
Nominal current IN		10 A	

EAC			RU C- DE.BL08.B.00714
-----	---	--	--------------------------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN		300 V	
Nominal current IN		10 A	

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN		300 V	
Nominal current IN		10 A	

cULus Recognized			
------------------	---	--	--