

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 6,3 x 32, nom. voltage: 250 V, nominal current: 10 A, connection method: Push-in connection, Rated cross section: 6 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup>- 10 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: black

## Your advantages

- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space

## Commercial Data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3212133             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales Key                            | BE2234              |
| Product Key                          | BE2234              |
| Catalog Page                         | Page 112 (C-1-2019) |
| GTIN                                 | 4046356494632       |
| Weight per Piece (including packing) | 26.611 g            |
| Weight per Piece (excluding packing) | 26.611 g            |
| Customs tariff number                | 85369095            |
| Country of origin                    | CN                  |

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Technical Data

### Notes

|         |   |
|---------|---|
| General | The current is determined by the fuse used, the voltage by the selected LED.<br>If the fuse is faulty, the downstream circuit will not be disconnected. |
|---------|---|

### Product properties

|                       |                     |
|-----------------------|---------------------|
| Product type          | Fuse terminal block |
| Number of connections | 2                   |
| Number of rows        | 1                   |
| Potentials            | 1                   |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |  |
|---|--|
| Fuse type                                       | Glass / ceramics / ...   |
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.31 W   |
| Fuse  | G / 6,3 x 32   |
| LED voltage range                               | 110 V AC/DC ... 250 V AC/DC (LED red)  |
| LED current range                               | 0.41 mA ... 0.96 mA  |
| Maximum power dissipation                       | max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload)<br>max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload)<br>max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit)<br>max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit) |

### Input data

|                   |                                       |
|-------------------|---------------------------------------|
| LED voltage range | 110 V AC/DC ... 250 V AC/DC (LED red) |
|-------------------|---------------------------------------|

### Connection data

|                                  |  |
|----------------------------------|--|
| Number of connections per level  | 2  |
| Nominal cross section            | 6 mm <sup>2</sup>                          |
| Rated cross section AWG          | 10   |
| Stripping length                 | 10 mm ... 12 mm                            |
| Internal cylindrical gage        | A5   |
| Connection in acc. with standard | IEC 60947-7-3                              |
| Conductor cross section solid    | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Cross section AWG                | 20 ... 8 (converted acc. to IEC)           |

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

|   |   |
|---|---|
| Conductor cross section flexible  | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>  |
| Conductor cross section, flexible [AWG]   | 20 ... 8 (converted acc. to IEC)  |
| Flexible conductor cross section flexible (ferrule, w/o plastic sleeve)                   | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Flexible conductor cross section (ferrule with plastic sleeve)                            | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> When using TWIN ferrules, we recommend a minimum ferrule length of 13 mm. |
| Nominal current   | 10 A  |
| Maximum load current  | 10 A (the current is determined by the fuse used)   |
| Nominal voltage   | 250 V   |
| Nominal cross section   | 6 mm <sup>2</sup>   |

## Connection cross sections directly pluggable

|   |  |
|---|--|
| Conductor cross section solid   | 1 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Flexible conductor cross section flexible (ferrule, w/o plastic sleeve) | 1 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| Flexible conductor cross section (ferrule with plastic sleeve)          | 1 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |

## Dimensions

|                  |         |
|------------------|---------|
| Width            | 8.2 mm  |
| End cover width  | 2.2 mm  |
| Height           | 61.5 mm |
| Height NS 35/15  | 76.5 mm |
| Height NS 35/7,5 | 69 mm   |
| Length           | 74.5 mm |

## Material specifications

|  |       |
|--|-------|
| Color                                  | black |
| Flammability rating according to UL 94 | V0    |
| Insulating material group              | I     |
| Insulating material                    | PA    |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-3 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |


# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Drawings

### Application drawing




Fuse terminal block in single arrangement,  
block consisting of one fuse terminal block and 4 feed-through terminal blocks

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

Circuit diagram




# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

Application drawing



Fuse terminal blocks in interconnected arrangement,  
block consisting of 5 fuse terminal blocks

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Approvals

| <br>Approval ID: TAE000010T |                       |                       |                   |                      |
|-----------------------------|-----------------------|-----------------------|-------------------|----------------------|
|                             | Nominal Voltage $U_N$ | Nominal Current $I_N$ | Cross Section AWG | Cross Section $mm^2$ |
|                             |                       |                       | -                 | -                    |

| <br>Approval ID: 13631 |                       |                       |                   |                      |
|------------------------|-----------------------|-----------------------|-------------------|----------------------|
|                        | Nominal Voltage $U_N$ | Nominal Current $I_N$ | Cross Section AWG | Cross Section $mm^2$ |
| Use group B            | 300 V                 | 10 A                  | 20 - 8            | -                    |
| Use group C            | 300 V                 | 10 A                  | 20 - 8            | -                    |
| Use group D            | 600 V                 | 5 A                   | 20 - 8            | -                    |

| <br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|---------------------------------------|--|--|--|--|
|---------------------------------------|--|--|--|--|

| <br>Approval ID: E60425 |                       |                       |                   |                      |
|-------------------------|-----------------------|-----------------------|-------------------|----------------------|
|                         | Nominal Voltage $U_N$ | Nominal Current $I_N$ | Cross Section AWG | Cross Section $mm^2$ |
| Use group B             | 300 V                 | 10 A                  | 20 - 8            | -                    |
| Use group C             | 300 V                 | 10 A                  | 20 - 8            | -                    |
| Use group D             | 600 V                 | 5 A                   | 20 - 8            | -                    |

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Classifications

### ECLASS

|               |          |
|---------------|----------|
| ECLASS-9.0    | 27141116 |
| ECLASS-10.0.1 | 27141116 |
| ECLASS-11.0   | 27141116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC000899 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Environmental Product Compliance


|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Accessories

 Note: Applying some accessories below might limit this product.


### Plug-in bridge

Plug-in bridge - FBS 2-8 - 3030284

<https://www.phoenixcontact.com/gb/products/3030284>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---

### Plug-in bridge

Plug-in bridge - FBS 3-8 - 3030297

<https://www.phoenixcontact.com/gb/products/3030297>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 4-8 - 3030307

<https://www.phoenixcontact.com/gb/products/3030307>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 5-8 - 3030310

<https://www.phoenixcontact.com/gb/products/3030310>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 20 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 6-8 - 3032470

<https://www.phoenixcontact.com/gb/products/3032470>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 10-8 - 3030323

<https://www.phoenixcontact.com/gb/products/3030323>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 2-8 CT - 3033830

<https://www.phoenixcontact.com/gb/products/3033830>



Plug-in bridge, pitch: 8.2 mm, color: orange

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 3-8 CT - 3033831

<https://www.phoenixcontact.com/gb/products/3033831>



Plug-in bridge, pitch: 8.2 mm, color: orange

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 4-8 CT - 3033832

<https://www.phoenixcontact.com/gb/products/3033832>



Plug-in bridge, pitch: 8.2 mm, color: orange

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 10-8 CT - 3033833

<https://www.phoenixcontact.com/gb/products/3033833>



Plug-in bridge, pitch: 8.2 mm, color: orange

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 2-8 BU - 3032567

<https://www.phoenixcontact.com/gb/products/3032567>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 3-8 BU - 3032570

<https://www.phoenixcontact.com/gb/products/3032570>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 4-8 BU - 3032583

<https://www.phoenixcontact.com/gb/products/3032583>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 5-8 BU - 3032596

<https://www.phoenixcontact.com/gb/products/3032596>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 6-8 BU - 3032677

<https://www.phoenixcontact.com/gb/products/3032677>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 10-8 BU - 3032606

<https://www.phoenixcontact.com/gb/products/3032606>



Plug-in bridge, pitch: 8.2 mm, color: blue

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 2-8 GY - 3032621

<https://www.phoenixcontact.com/gb/products/3032621>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 3-8 GY - 3032622

<https://www.phoenixcontact.com/gb/products/3032622>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 4-8 GY - 3032635

<https://www.phoenixcontact.com/gb/products/3032635>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 5-8 GY - 3032648

<https://www.phoenixcontact.com/gb/products/3032648>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBS 6-8 GY - 3032664

<https://www.phoenixcontact.com/gb/products/3032664>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBS 10-8 GY - 3032651

<https://www.phoenixcontact.com/gb/products/3032651>



Plug-in bridge, pitch: 8.2 mm, color: gray

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBSR 2-8 - 3033808

<https://www.phoenixcontact.com/gb/products/3033808>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBSR 3-8 - 3001597

<https://www.phoenixcontact.com/gb/products/3001597>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBSR 4-8 - 3000585

<https://www.phoenixcontact.com/gb/products/3000585>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBSR 5-8 - 3033809

<https://www.phoenixcontact.com/gb/products/3033809>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Plug-in bridge

Plug-in bridge - FBSR 10-8 - 3001599

<https://www.phoenixcontact.com/gb/products/3001599>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---


## Plug-in bridge

Plug-in bridge - FBSR 16-8 - 3033816

<https://www.phoenixcontact.com/gb/products/3033816>



Plug-in bridge, pitch: 8.2 mm, color: red

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Switching jumper

Switching jumper - SB-MER 2-8 - 3000587

<https://www.phoenixcontact.com/gb/products/3000587>



Switching jumper, pitch: 8.2 mm, color: gray/orange

 Max. current carrying capacity: 30 A

---


## Switching jumper

Switching jumper - SB-MER 3-8 - 3000588

<https://www.phoenixcontact.com/gb/products/3000588>



Switching jumper, pitch: 8.2 mm, color: gray/orange

 Max. current carrying capacity: 30 A

---

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>


## Switching jumper

Switching jumper - SB-MER 4-8 - 3000589

<https://www.phoenixcontact.com/gb/products/3000589>



Switching jumper, pitch: 8.2 mm, color: gray/orange

 Max. current carrying capacity: 30 A

---

## Partition plate

Partition plate - ATP-ST 4 - 3030721

<https://www.phoenixcontact.com/gb/products/3030721>



Partition plate, length: 59.8 mm, width: 2 mm, height: 39 mm, color: gray

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Screwdriver

Screwdriver - SZF 1-0,6X3,5 - 1204517

<https://www.phoenixcontact.com/gb/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

## Mounting material

Mounting material - PT-IL - 3208090

<https://www.phoenixcontact.com/gb/products/3208090>

Operating decal for the push-in Technology



# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Actuation tool

Actuation tool - ST-BW - 1207608

<https://www.phoenixcontact.com/gb/products/1207608>

Actuation tool, for all 2.5 mm<sup>2</sup> - 4.0 mm<sup>2</sup> spring-cages



---

## Warning label

Warning label - WS PT 6 - 1029029

<https://www.phoenixcontact.com/gb/products/1029029>

Warning label, yellow/black, labeled: Lightning flash, mounting type: plug in, for terminal block width: 8.2 mm



# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail perforated

DIN rail perforated - NS 35/ 7,5 PERF 2000MM - 0801733

<https://www.phoenixcontact.com/gb/products/0801733>



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 UNPERF 2000MM - 0801681

<https://www.phoenixcontact.com/gb/products/0801681>



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver, Pack of 25 (50 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail perforated

DIN rail perforated - NS 35/ 7,5 WH PERF 2000MM - 1204119

<https://www.phoenixcontact.com/gb/products/1204119>



DIN rail perforated, acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - 1204122

<https://www.phoenixcontact.com/gb/products/1204122>



DIN rail, unperforated, acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver, Pack of 10 (20 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 AL UNPERF 2000MM - 0801704

<https://www.phoenixcontact.com/gb/products/0801704>



DIN rail, unperforated, acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail perforated

DIN rail perforated - NS 35/ 7,5 ZN PERF 2000MM - 1206421

<https://www.phoenixcontact.com/gb/products/1206421>



DIN rail perforated, acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver, Pack of 25 (50 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 ZN UNPERF 2000MM - 1206434

<https://www.phoenixcontact.com/gb/products/1206434>



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail, unperforated

DIN rail, unperforated - NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - 0801762

<https://www.phoenixcontact.com/gb/products/0801762>



DIN rail, unperforated, acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored, Pack of 10 (20 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## End cap

End cap - NS 35/ 7,5 CAP - 1206560

<https://www.phoenixcontact.com/gb/products/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



---

## DIN rail perforated

DIN rail perforated - NS 35/15 PERF 2000MM - 1201730

<https://www.phoenixcontact.com/gb/products/1201730>



DIN rail perforated, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver, Pack of 25 (50 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714

<https://www.phoenixcontact.com/gb/products/1201714>



DIN rail, unperforated, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail perforated

DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602

<https://www.phoenixcontact.com/gb/products/0806602>



DIN rail perforated, similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: white, Pack of 25 (50 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15 WH UNPERF 2000MM-VPE 10 - 1204135

<https://www.phoenixcontact.com/gb/products/1204135>



DIN rail, unperforated, similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver, Pack of 10 (20 m)

---

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756

<https://www.phoenixcontact.com/gb/products/1201756>



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail perforated

DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

<https://www.phoenixcontact.com/gb/products/1206599>



DIN rail perforated, similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver, Pack of 25 (50 m)

---

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15 ZN UNPERF 2000MM - 1206586

<https://www.phoenixcontact.com/gb/products/1206586>



DIN rail, unperforated, similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver, Pack of 25 (50 m)

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM-VPE 10 - 1201895

<https://www.phoenixcontact.com/gb/products/1201895>



DIN rail, unperforated, similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored, Pack of 10 (20 m)

---

## End cap

End cap - NS 35/15 CAP - 1206573

<https://www.phoenixcontact.com/gb/products/1206573>

DIN rail end piece, for DIN rail NS 35/15



# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## DIN rail, unperforated

DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM-VPE 10 - 1201798

<https://www.phoenixcontact.com/gb/products/1201798>



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver, Pack of 10 (20 m)

---

## Zack marker strip

Zack marker strip - ZB 6:UNBEDRUCKT - 1051003

<https://www.phoenixcontact.com/gb/products/1051003>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack marker strip

Zack marker strip - ZB 6 CUS - 0824992

<https://www.phoenixcontact.com/gb/products/0824992>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## Zack marker strip

Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN - 1051016

<https://www.phoenixcontact.com/gb/products/1051016>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack marker strip

Zack marker strip - ZB 6,QR:FORTL.ZAHLEN - 1051029

<https://www.phoenixcontact.com/gb/products/1051029>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## Zack marker strip

Zack marker strip - ZB 6,LGS:GLEICHE ZAHLEN - 1051032

<https://www.phoenixcontact.com/gb/products/1051032>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: Identical numbers 1 or 2, etc. up to 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - ZB 6,LGS:L1-N,PE - 1051414

<https://www.phoenixcontact.com/gb/products/1051414>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## Marker for terminal blocks

Marker for terminal blocks - ZB 6,LGS:U-N - 1051430

<https://www.phoenixcontact.com/gb/products/1051430>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: U, V, W, N, GND, U, V, W, N, GND, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UC-TM 6 - 0818085

<https://www.phoenixcontact.com/gb/products/0818085>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

---

## Marker for terminal blocks

Marker for terminal blocks - UC-TM 6 CUS - 0824589

<https://www.phoenixcontact.com/gb/products/0824589>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UCT-TM 6 - 0828736

<https://www.phoenixcontact.com/gb/products/0828736>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

---

## Marker for terminal blocks

Marker for terminal blocks - UCT-TM 6 CUS - 0829602

<https://www.phoenixcontact.com/gb/products/0829602>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6:UNBEDRUCKT - 0808710

<https://www.phoenixcontact.com/gb/products/0808710>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

---

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6 CUS - 0825027

<https://www.phoenixcontact.com/gb/products/0825027>



Zack Marker strip, flat, Strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UC-TMF 6 - 0818140

<https://www.phoenixcontact.com/gb/products/0818140>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 5.1 mm, Number of individual labels: 80

---

## Marker for terminal blocks

Marker for terminal blocks - UC-TMF 6 CUS - 0824646

<https://www.phoenixcontact.com/gb/products/0824646>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 5.1 mm, Number of individual labels: 80

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UCT-TMF 6 - 0828746

<https://www.phoenixcontact.com/gb/products/0828746>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.4 x 4.7 mm, Number of individual labels: 60

---

## Marker for terminal blocks

Marker for terminal blocks - UCT-TMF 6 CUS - 0829665

<https://www.phoenixcontact.com/gb/products/0829665>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 5.4 x 4.7 mm, Number of individual labels: 60

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6,LGS:FORTL.ZAHLEN - 0808749

<https://www.phoenixcontact.com/gb/products/0808749>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

---

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6,QR:FORTL.ZAHLEN - 0808765

<https://www.phoenixcontact.com/gb/products/0808765>



Zack Marker strip, flat, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6,LGS:GERADE ZAHLEN - 0810834

<https://www.phoenixcontact.com/gb/products/0810834>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive even numbers 2 ... 20, 22 ... 40, etc. up to 82 ... 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

---

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 6,LGS:UNGERADE ZAHLEN - 0810876

<https://www.phoenixcontact.com/gb/products/0810876>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: Odd numbers 1 - 19, 21 - 39, etc. up to 81 - 99, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 8:UNBEDRUCKT - 0808781

<https://www.phoenixcontact.com/gb/products/0808781>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

---

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 8 CUS - 0825030

<https://www.phoenixcontact.com/gb/products/0825030>



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Zack Marker strip, flat

Zack Marker strip, flat - ZBF 8,LGS:FORTL.ZAHLEN - 0808804

<https://www.phoenixcontact.com/gb/products/0808804>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 101 ... 110, mounting type: snapped, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

---

## Marker for terminal blocks

Marker for terminal blocks - UC-TMF 8 - 0818137

<https://www.phoenixcontact.com/gb/products/0818137>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.6 x 5.1 mm, Number of individual labels: 56

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UC-TMF 8 CUS - 0824654

<https://www.phoenixcontact.com/gb/products/0824654>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 5.1 mm, Number of individual labels: 56

---

## Marker for terminal blocks

Marker for terminal blocks - UCT-TMF 8 - 0828748

<https://www.phoenixcontact.com/gb/products/0828748>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.4 x 4.7 mm, Number of individual labels: 42

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - UCT-TMF 8 CUS - 0829672

<https://www.phoenixcontact.com/gb/products/0829672>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8.2 mm, lettering field size: 7.4 x 4.7 mm, Number of individual labels: 42

---

## Insulating sleeve

Insulating sleeve - ISH 4/0,5 - 3002885

<https://www.phoenixcontact.com/gb/products/3002885>



Insulating sleeve, color: gray

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Insulating sleeve

Insulating sleeve - ISH 4/1,0 - 3002898

<https://www.phoenixcontact.com/gb/products/3002898>



Insulating sleeve, color: black

---

## Software

Software - PROJECT COMPLETE - 1050453

<https://www.phoenixcontact.com/gb/products/1050453>



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - TMT 6 R - 0816498

<https://www.phoenixcontact.com/gb/products/0816498>



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK S1.1, perforated, mounting type: snapped, snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 6.35 x 6.15 mm, Number of individual labels: 16000

---

## Marker for terminal blocks

Marker for terminal blocks - TMT 6 R CUS - 0824488

<https://www.phoenixcontact.com/gb/products/0824488>



Marker for terminal blocks, can be ordered: by line, white, labeled according to customer specifications, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 6.35 x 6.15 mm

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## Marker for terminal blocks

Marker for terminal blocks - TMT (EX9,5)R - 0828295

<https://www.phoenixcontact.com/gb/products/0828295>



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: snapped, snap into tall marker groove, lettering field size: 9.5 x 50000 mm, Number of individual labels: 1

---

## Marker for terminal blocks

Marker for terminal blocks - US-TM 100 - 0829255

<https://www.phoenixcontact.com/gb/products/0829255>



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, lettering field size: 104 x 9.8 mm, Number of individual labels: 13

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)

3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## End clamp

End clamp - CLIPFIX 35 - 3022218

<https://www.phoenixcontact.com/gb/products/3022218>



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray

---

## End clamp

End clamp - CLIPFIX 35-5 - 3022276

<https://www.phoenixcontact.com/gb/products/3022276>



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray

# Fuse modular terminal block - PT 6-HESILED 250 (6,3X32)



3212133

<https://www.phoenixcontact.com/gb/products/3212133>

## End clamp

End clamp - E/NS 35 N - 0800886

<https://www.phoenixcontact.com/gb/products/0800886>

End clamp, width: 9.5 mm, color: gray



---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)