

## Protective hose - WP-PA HF-SL 34,5 BK - 3240847

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide protective hose, inflammability class V0, UV resistant

RoHS

### Key Commercial Data

Packing unit	1 M
Minimum order quantity	10 M
GTIN	 4 046356 736633
GTIN	4046356736633
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	39173200
Country of origin	Germany

### Technical data

#### Dimensions

Inner diameter (f)	29 mm
Outside diameter	34.5 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Short-term temperature	120 °C
Degree of protection	IP67

#### General

Color	black
Type	Helically corrugated plastic hose

# Protective hose - WP-PA HF-SL 34,5 BK - 3240847

## Technical data

### General

Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	HB
Material	PA
Bending radius, static	55 mm
Bending radius, dynamic	170 mm
Tensile strength	100 N

### Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.1	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27430304
eCl@ss 8.0	27430304
eCl@ss 9.0	27430304

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177
ETIM 6.0	EC001177
ETIM 7.0	EC001177

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411

# Protective hose - WP-PA HF-SL 34,5 BK - 3240847

## Classifications

### UNSPSC

UNSPSC 13.2	40141734
-------------	----------

## Approvals

### Approvals

---

### Approvals


UL Recognized

---

Ex Approvals

---

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
---------------	--	---

---