

## Fork-type cable lug - C-FC 6/M4 - 3240148

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fork-type cable lug, non-insulated, 2.6 - 6 mm<sup>2</sup>, M4

### Why buy this product

- ✓ The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- ✓ The insulated versions are halogen-free and feature "EASY ENTRY" technology

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 453653
GTIN	4046356453653
Weight per Piece (excluding packing)	1.600 g
Custom tariff number	85369010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	19.5 mm
Width (a)	8.2 mm
Maximum stripping length	9 mm
Length of insulation sleeve (c)	6.5 mm
Inner dimension of the insulating collar (d)	3.6 mm
Distance between the center and the insulation sleeve (e)	7.5 mm

# Fork-type cable lug - C-FC 6/M4 - 3240148

## Technical data

### Dimensions

Inner diameter (f)	4.3 mm
Material thickness (g)	1 mm

### Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

### General

Color	silver
Stripping length	9 mm
Components	halogen-free
Material	Copper
Coating	tin-plated

### Standards and Regulations


Design according to standard	DIN 46234
------------------------------	-----------

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 8.0	27400204
eCl@ss 9.0	27400203

## Fork-type cable lug - C-FC 6/M4 - 3240148

### Classifications

#### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052
ETIM 6.0	EC001052

#### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121707

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

---

#### Approval details

EAC		7500651.22.01.00246
-----	-------------------------------------------------------------------------------------	---------------------