

## Cable binder base - WT-BASE HF 9 - 3240704

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binder base, for cable binders up to 9 mm wide, screwable, 5 mm fixing hole, 2-sided cable binder feed-through

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	1.4 g
Custom tariff number	39269097
Country of origin	Italy

### Technical data

#### Dimensions

Length (b)	22.5 mm
Width (a)	14.6 mm
Height	11 mm
Hole diameter	5.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

#### General

Color	transparent
Type	Fixing
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA 6.6

#### Standards and Regulations

Flammability rating according to UL 94	V2
--	----

## Cable binder base - WT-BASE HF 9 - 3240704

### Classifications

#### eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

#### ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703