

Printed-circuit board connector - PTF 0,3/ 4-WB-1,8-H - 1826114


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 10 A, Rated voltage (III/2): 25 V, Number of positions: 4, Pitch: 1.8 mm, Color: White, Contact surface: Silver



Key commercial data

Packing unit	1 PCE
Minimum order quantity	250 PCE
GTIN	 4 046356 834025
Custom tariff number	85444290
Country of origin	GERMANY

Technical data

Dimensions

Pitch	1.8 mm
Dimension a	5.4 mm

General

Range of articles	PTF 0,3/..-WB-H
Insulating material group	IIIa
Rated voltage (III/3)	25 V
Rated voltage (III/2)	25 V
Rated voltage (II/2)	25 V
Nominal current I_N	10 A
Nominal cross section	0.34 mm ²
Maximum load current	10 A (Total current of all contacts)
Insulating material	PBT
Inflammability class according to UL 94	V0

Printed-circuit board connector - PTF 0,3/ 4-WB-1,8-H - 1826114

Technical data

General

Number of positions	4
---------------------	---

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC


UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432
UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432

eCl@ss

eCl@ss 4.0	27141111
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

Drawings

Dimensioned drawing



Dimension L: 500 mm

Dimensioned drawing

